

**350W** Fan cooled


**200W** Conduction cooled

AC-DC power supplies

The GCS350 is a series of medical AC-DC power supplies with 350W fan cooled and 200W convection rating.

Designed to minimize no load power consumption, the GCS350 series of high efficiency, single-output power supplies are packaged in an industry standard 127.0 x 76.2 x 36.3mm package making them suitable for medical, industrial, information technology and domestic applications. Class I and Class II versions are available, allowing use in professional healthcare facilities such as hospitals and remotely in patients' homes or workplaces.


With a wide range of international medical safety and ITE approvals, class B compliance for conducted and radiated emissions, very low earth leakage currents, and 2 x MOPP protection, the GCS350 benefits system designers with easy integration into a wide range of applications.



## Features

- ▶ Single outputs from 12V to 56VDC
- ▶ Universal 85 to 264VAC input range
- ▶ High efficiency – up to 93%
- ▶ ITE and medical safety approvals (Class I & II)
- ▶ 4kVAC input to output isolation
- ▶ Class B conducted emissions
- ▶ Remote On/Off, 12VDC 0.6A fan supply
- ▶ Overcurrent, overvoltage and short-circuit protection
- ▶ -40°C to +70°C operating temperature
- ▶ 3 year warranty

## Applications



## Dimensions

127.0 x 76.2 x 36.3mm (5.00" x 3.00" x 1.42")  
 (-C): 139.7 x 88.5 x 43.2mm (5.50" x 3.48" x 1.70")  
 (-TF): 139.7 x 88.5 x 57.8mm (5.50" x 3.48" x 2.20")  
 (-EF): 152.4 x 88.9 x 44.4mm (6.00" x 3.50" x 1.75")

## More resources

Click the link or scan the code

→ [xppower.com](http://xppower.com)



## Models & ratings

| Model number <sup>(1,2,3)</sup> | Output voltage V1 | Output current (V1)                |                           | Output voltage (Vfan) & Current | Max output power |
|---------------------------------|-------------------|------------------------------------|---------------------------|---------------------------------|------------------|
|                                 |                   | Convection cooled <sup>(4,5)</sup> | Fan cooled <sup>(6)</sup> |                                 |                  |
| GCS350PS12                      | 12.0VDC           | 16.7A                              | 29.2A                     | 12.0VDC/0.6A                    | 350W             |
| GCS350PS15                      | 15.0VDC           | 13.3A                              | 23.4A                     | 12.0VDC/0.6A                    | 350W             |
| GCS350PS24                      | 24.0VDC           | 8.3A                               | 14.6A                     | 12.0VDC/0.6A                    | 350W             |
| GCS350PS28                      | 28.0VDC           | 7.1A                               | 12.5A                     | 12.0VDC/0.6A                    | 350W             |
| GCS350PS48                      | 48.0VDC           | 4.2A                               | 7.3A                      | 12.0VDC/0.6A                    | 350W             |
| GCS350PS56                      | 56.0VDC           | 3.6A                               | 6.25A                     | 12.0VDC/0.6A                    | 350W             |

### Notes:

1. Add suffix -C for convection-cooled cover, e.g. GCS350PS12-C.
2. Cover kits available. Order part no.: GCS150/180 CVR KIT.
3. Add suffix -EF for fan cooled cover with end fan e.g. GCS350PS12-EF, add suffix -TF for fan cooled cover with top fan, e.g. GCS350PS12-TF. Note: Vfan output no longer available.
4. Convection rating quoted at +40°C, see thermal derating curve.
5. GCS350-C models derate 15% when convection cooled at +40°C.
6. 424.75 L/M (15CFM) required to meet stated current.
7. Add suffix '-J' for optional dual row molex connector. See mechanical details.
8. Add suffix '-S' for optional screw terminals. See mechanical details.

## Summary


| Characteristic        | Minimum   | Typical | Maximum | Units | Notes & conditions                        |
|-----------------------|---|---------|---------|-------|---|
| Input voltage range   | 85  | 115/230 | 264     | VAC   | Derate output power at <90VAC. See fig. 1 |
| No load input power   |   | 4       |         | W     | 115/230VAC                                |
| Efficiency            |   | 93      |         | %     | 230VAC Full load (see fig.3-5 )           |
|                       | 80 plus silver  |         |         |       | All models except 12V models              |
|                       | 80 plus bronze  |         |         |       | 12V models                                |
| Operating temperature | -40   |         | +70     | °C    | See derating curve, fig. 8                |
| Emc                   | EN55011/32 Level B Conducted & Level A Radiated, EN61000-3-3  |         |         |       |   |
| Safety approvals      | IEC60950-1, IEC60601-1, UL62368-1, CAN/CSA C22.2 No. 62368-1-14, ANSI/AAMI ES60601-1, CSA C22.2, No.60601-1, EN62368-1, EN60601-1 |         |         |       |   |

## Input

| Characteristic            | Minimum                                | Typical | Maximum | Units | Notes & conditions                       |
|---------------------------|--|---------|---------|-------|--|
| Input voltage range       | 85                                     | 115/230 | 264     | VAC   | Derate output power at 90VAC. See fig. 1 |
| Input frequency           | 47                                     | 50/60   | 63      | Hz    |  |
| Power factor              |  | >0.9    |         |       | 230VAC, 100% load                        |
| Input current - full load |  | 3.6/1.8 |         | A     | 115/230VAC                               |
| Inrush current            |  | 80      |         | A     | 230VAC, cold start +25°C                 |
| Earth leakage current     |  | 95/185  | 250     | µA    | 115/230VAC/50Hz Typ., 264VAC/60Hz max.   |
| No load input power       |  | 4       |         | W     | 115/230VAC                               |
| Input protection          | F5.0A/250V internal fuse in both lines |         |         |       |  |

## Input voltage derating curve

Figure 1




## Output

| Characteristic                 | Minimum | Typical | Maximum                             | Units           | Notes & conditions  |
|--------------------------------|---------|---------|-------------------------------------|-----------------|---|
| Output voltage V1              | 12      |         | 56                                  | VDC             | See Models & Ratings table  |
| Initial set accuracy           |         |         | $\pm 1^{(V1)}$ & $\pm 5^{(Vfan)}$   | %               | 50% load, 115/230VAC  |
| Output voltage adjustment (V1) |         |         | $\pm 2$                             | %               | Via potentiometer. See mech. details, Vfan will track                         |
| Minimum load                   | 0       |         |                                     | A               | No minimum load required  |
| Start up delay                 |         |         | 2                                   | s               | 115/230VAC, full load   |
| Hold up time                   |         | 17      |                                     | ms              |   |
| Drift                          |         |         | $\pm 0.2$                           | %               | After 20 min warm up  |
| Line regulation                |         |         | $\pm 0.5$                           | %               | 90-264VAC   |
| Load regulation                |         |         | $\pm 0.5^{(V1)}$ , $\pm 5^{(Vfan)}$ | %               | 0-100% load   |
| Transient response (V1)        |         |         | 4                                   | %               | Recovery within 1% in less than 500 $\mu$ s for a 50-75% and 75-50% load step |
| Over/undershoot (V1)           |         | 0       |                                     | %               |   |
| Ripple & noise (V1)            |         |         | 1                                   | % pk-pk         | 20MHz bandwidth, 12V models 1.5% max.   |
| Overvoltage protection (V1)    | 110     |         | 140                                 | %               | Vnom DC. Output (V1), recycle input to reset                                  |
| Overload protection (V1)       | 110     |         | 150                                 | % I nom         | See fig. 2. Trip & restart  |
| Short circuit protection (V1)  |         |         |                                     |                 | Continuous  |
| Temperature coefficient        |         |         | 0.05                                | %/ $^{\circ}$ C |   |
| Overtemperature protection     |         |         | 110                                 | $^{\circ}$ C    | Measured internally, auto resetting   |

### Output overload characteristic

Figure 2  
GCS350PS12 example (others similar)



## General

| Characteristic  | Minimum        | Typical     | Maximum | Units             | Notes & conditions               |
|---|----------------|-------------|---------|-------------------|----------------------------------|
| Efficiency  |                | 93          |         | %                 | 230VAC Full load (see fig.3-5 )  |
|   | 80 plus silver |             |         |                   | All models except 12V models     |
|   | 80 plus bronze |             |         |                   | 12V models                       |
| Isolation: Input to output<br>Input to ground<br>Output to ground | 4000           |             |         | VAC               |                                  |
|   | 1500           |             |         |                   |                                  |
|   | 1500           |             |         |                   |                                  |
| Switching frequency   | 60             |             | 200     | kHz               | PFC                              |
|   | 90             |             | 150     |                   | Main converter                   |
| Power density   |                |             | 16.4    | W/in <sup>3</sup> |                                  |
| Mean time between failure   |                | 569         |         | khrs              | MIL-HDBK-217F, Notice 2 +25°C GB |
| Weight  |                | 0.65 (0.29) |         | lb (kg)           | Open frame                       |
|   |                | 1.30 (0.59) |         |                   | End fan unit                     |
|   |                | 1.15 (0.52) |         |                   | Top fan unit                     |
|   |                | 1.05 (0.48) |         |                   | Covered unit                     |

## Efficiency graphs

### Efficiency vs load

Figure 3  
GCS350PS12




Figure 4  
GCS350PS24





Figure 5  
GCS350PS48




## Signals & controls

| Characteristic |         | Notes & conditions  |
|----------------|---------|---|
| Remote sense   |         | Compensates for 0.5V total voltage drop   |
| Remote On/Off  | Inhibit | The inhibit lo (pin 4), should be pulled below 0.4V to switch V1 & Vfan off. Open circuit or >4V to switch on (see fig. 6)                                |
|                | Enable  | With the inhibit lo (pin 4) pulled low as detailed above, connecting inhibit hi (pin 5) to inhibit lo (pin 4) will enable V1 & V fan output. (see fig. 7) |


### Remote On/Off (Inhibit)

Figure 6



### Remote On/Off (Enable)

Figure 7



## Environmental

| Characteristic        | Minimum   | Typical | Maximum | Units | Notes & conditions                |
|-----------------------|---|---------|---------|-------|-----------------------------------|
| Operating temperature | -40   |         | +70     | °C    | See derating curves, fig. 8 and 9 |
| Storage temperature   | -40   |         | +85     | °C    |                                   |
| Cooling               | 15  |         |         | CFM   |                                   |
| Humidity              | 5   |         | 95      | %RH   | Non-condensing                    |
| Operating altitude    |   |         | 5000    | m     |                                   |
| Shock                 | ±3 x 30g shocks in each plane, total 18 shocks. 30g = 11ms (±0.5msec), half sine. Conforms to EN60068-2-27 & EN60068-2-47 |         |         |       |                                   |
| Vibration             | Single axis 10-500 Hz at 2g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6                     |         |         |       |                                   |

### Temperature derating curve

Figure 8 - Convection cooled ratings





Figure 9 - Fan cooled ratings



## EMC: emissions

| Phenomenon            | Standard    | Test level | Notes & conditions |
|-----------------------|-------------|------------|--------------------|
| Conducted             | EN55011/32  | Class B    |                    |
| Radiated              | EN55011/32  | Class A    |                    |
| Harmonic fluctuations | EN61000-3-3 |            |                    |

## EMC: immunity

| Phenomenon              | Standard                | Test level              | Criteria | Notes & conditions          |
|-------------------------|-------------------------|-------------------------|----------|-----------------------------|
| Low voltage PSU EMC     | EN61204-3               | High severity level     | as below |                             |
| Harmonic current        | EN61000-3-2             | Class A                 | A        | All models                  |
|                         |                         | Class C                 |          | >125W                       |
| Radiated                | EN61000-4-3             | 3                       | A        |                             |
| EFT                     | EN61000-4-4             | 3                       | A        |                             |
| Surges                  | EN61000-4-5             | Installation class 3    | A        |                             |
| Conducted               | EN61000-4-6             | 3                       | A        |                             |
| Dips and interruptions  | EN55035<br>(100VAC)     | Dip >95% (0VAC), 8.3ms  | A        |                             |
|                         |                         | Dip 30% (70VAC), 416ms  | B        |                             |
|                         |                         | Dip >95% (0VAC), 4160ms | B        |                             |
|                         | EN55035<br>(240VAC)     | Dip >95% (0VAC), 10.0ms | A        |                             |
|                         |                         | Dip 30% (168VAC), 500ms | B        |                             |
|                         |                         | Dip >95% (0VAC), 5000ms | B        |                             |
|                         | EN60601-1-2<br>(100VAC) | Dip >95% (0VAC), 10.0ms | A        |                             |
|                         |                         | Dip 60% (40VAC), 100ms  | A        | Derate Output Power to 150W |
|                         |                         | Dip 30% (70VAC), 500ms  | A        |                             |
|                         | EN60601-1-2<br>(240VAC) | Dip >95% (0VAC), 5000ms | B        |                             |
|                         |                         | Dip >95% (0VAC), 10.0ms | A        |                             |
|                         |                         | Dip 60% (96VAC), 100ms  | A        |                             |
| Dip 30% (168VAC), 500ms |                         | A                       |          |                             |
|                         |                         | Dip >95% (0VAC), 5000ms | B        |                             |


## Safety approvals

| Certification              | Standard  | Notes & conditions  |
|----------------------------|---|---|
| CB                         | IEC60950-1:2005 Ed 2 / IEC62368-1:2014              | Information Technology                                    |
|                            | IEC60601-1 Ed 3.1 Including Risk Management         | Medical   |
| UL                         | UL62368-1 & CAN/CSA C22.2 No. 62368-1-14            | Information Technology                                    |
|                            | ANSI/AAMI ES60601-1:2005 & CSA C22.2, No.60601-1:08 | Medical   |
| TUV                        | EN62368-1:2014/A11:2017                             | Information Technology                                    |
|                            | EN60601-1/A12:2016                                  | Medical   |
| Equipment protection class | Class I & Class II                                  | See safety agency conditions of acceptability for details |
| CE                         | Meets all applicable directives                     |   |
| UKCA                       | Meets all applicable legislation                    |   |


| Isolation            | Means of protection                    | Category   |
|----------------------|--|------------|
| Primary to secondary | 2 x MOPP (Means of Patient Protection) | IEC60601-1 |
| Primary to earth     | 1 x MOPP (Means of Patient Protection) | IEC60601-1 |
| Secondary to earth   | 1 x MOPP (Means of Patient Protection) | IEC60601-1 |

## Mechanical details


Note: Mounting points A should be connected together for optimum EMI performance



M3 screw terminal bus bar  
Standard on 12/15 V models  
Optional on all other models,  
add suffix '-S' e.g. GCS350PS24-S



6 Position single row  
Standard on 24/28/48/56 V models



12 Position dual row  
Optional on 12/15 V models, add suffix  
'-J' e.g. GCS350PS12-J

| Input Connector J1 |          |
|--------------------|----------|
| Pin                | Function |
| 1                  | Line     |
| 2                  | Neutral  |

| Output Connector J2<br>6 Position<br>Molex pn. 09-65-2068 |          |
|---|----------|
| Pin   | Function |
| 1   | +V1      |
| 2   | +V1      |
| 3   | +V1      |
| 4   | RTN      |
| 5   | RTN      |
| 6   | RTN      |

| Output Connector J2<br>12 Position<br>Molex pn. 39-28-8120 |          |     |          |
|--|----------|-----|----------|
| Pin  | Function | Pin | Function |
| 1  | RTN      | 7   | RTN      |
| 2  | RTN      | 8   | RTN      |
| 3  | RTN      | 9   | RTN      |
| 4  | +V1      | 10  | +V1      |
| 5  | +V1      | 11  | +V1      |
| 6  | +V1      | 12  | +V1      |

| Fan Connector J3<br>Molex pn. 22-04-1021 |             |
|--|-------------|
| Pin                                      | Function    |
| 1  | Fan + (12V) |
| 2  | Fan -       |

| Signal Connector J4<br>Molex pn. B10B-PHDSS |                 |     |          |
|---|-----------------|-----|----------|
| Pin   | Function        | Pin | Function |
| 1   | +Sense          | 6   | N/C      |
| 2   | -Sense          | 7   | N/C      |
| 3   | XP Internal Use | 8   | N/C      |
| 4   | Inhibit LO      | 9   | N/C      |
| 5   | Inhibit HI      | 10  | N/C      |


### Notes:

- All dimensions in mm (inches).
- Tolerance x.xx (x.x) = 0.50 ( $\pm$ 0.02); x.xxx (x.xx) = 0.25 ( $\pm$ 0.01).
- Weight: 0.29kg (0.65lbs).
- J1 mates with Molex Housing Pn. 09-50-1031. 6 position single row J2 mates with Molex Housing Pn. 09-50-1061 and with Molex series 5194 crimp terminals. 12

position dual row J2 mates with Molex Housing Pn. 39-01-2125 and with Molex series 5556 crimp terminals. J3 mates with Molex Housing Pn. 51191-0200 and with Molex series 50802 crimp terminals. J4 mates with JST Housing Pn. PHDR-10VS and with JST SPHD-001T-P0.5 crimp terminals.

## Mechanical details

Covered version (-C suffix)



| Input Connector J1 |          |
|--------------------|----------|
| Pin                | Function |
| 1                  | Line     |
| 2                  | Neutral  |

| Output Connector J2<br>6 Position<br>Molex pn. 09-65-2068 |          |
|---|----------|
| Pin   | Function |
| 1   | +V1      |
| 2   | +V1      |
| 3   | +V1      |
| 4   | RTN      |
| 5   | RTN      |
| 6   | RTN      |

| Fan Connector J3<br>Molex pn. 22-04-1021 |             |
|--|-------------|
| Pin                                      | Function    |
| 1  | Fan + (12V) |
| 2  | Fan -       |

| Signal Connector J4<br>Molex pn. B10B-PHDSS |                 |     |          |
|---|-----------------|-----|----------|
| Pin   | Function        | Pin | Function |
| 1   | +Sense          | 6   | N/C      |
| 2   | -Sense          | 7   | N/C      |
| 3   | XP Internal Use | 8   | N/C      |
| 4   | Inhibit LO      | 9   | N/C      |
| 5   | Inhibit HI      | 10  | N/C      |


### Notes:

- All dimensions in mm (inches).
- Tolerance x.xx (x.x) = 0.50 (0.02); x.xxx (x.xx) = 0.25 (0.01).
- J1 mates with Molex Housing Pn. 09-50-1031. J2 mates with Molex Housing Pn. 09-50-1061 and with Molex series 5194 crimp terminals. J4 mates with JST Housing Pn. PHDR-10VS and with JST SPHD-001T-P0.5 crimp terminals. J3 mates with Molex Housing Pn. 51191-0200 and with Molex series 50802 crimp terminals.
- In class II installations the cover is floating and provides 1 x MOPP (2 x MOOP).
- Weight: 0.48kg (1.05lbs).
- The output connection options mentioned on page 7 are also available for this kind of enclosure.



## Mechanical details

### Top fan version (-TF suffix)



| Input Connector J1 |          |
|--------------------|----------|
| Pin                | Function |
| 1                  | Line     |
| 2                  | Neutral  |

| Output Connector J2<br>6 Position<br>Molex pn. 09-65-2068 |          |
|---|----------|
| Pin   | Function |
| 1   | +V1      |
| 2   | +V1      |
| 3   | +V1      |
| 4   | RTN      |
| 5   | RTN      |
| 6   | RTN      |

| Fan Connector J3<br>Molex pn. 22-04-1021 |             |
|--|-------------|
| Pin                                      | Function    |
| 1  | Fan + (12V) |
| 2  | Fan -       |


| Signal Connector J4<br>Molex pn. B10B-PHDSS |                 |     |          |
|---|-----------------|-----|----------|
| Pin   | Function        | Pin | Function |
| 1   | +Sense          | 6   | N/C      |
| 2   | -Sense          | 7   | N/C      |
| 3   | XP Internal Use | 8   | N/C      |
| 4   | Inhibit LO      | 9   | N/C      |
| 5   | Inhibit HI      | 10  | N/C      |

### Notes:

- All dimensions in mm (inches).
- Tolerance x.xx (x.x) = 0.50 (0.02); x.xxx (x.xx) = 0.25 (0.01).
- J1 mates with Molex Housing Pn. 09-50-1031. J2 mates with Molex Housing Pn. 09-50-1061 and with Molex series 5194 crimp terminals. J4 mates with JST Housing Pn. PHDR-10VS and with JST SPHD-001T-P0.5 crimp terminals. J3 mates with Molex Housing Pn. 51191-0200 and with Molex series 50802 crimp terminals.
- In class II installations the cover is floating and provides 1 x MOPP (2 x MOPP).
- Weight: 0.52kg (1.15lbs).
- The output connection options mentioned on page 7 are also available for this kind of enclosure.

## Mechanical details

### End fan version (-EF suffix)



| Input Connector J1<br>Dinkle pn. DT-2C-<br>A02W-03 |          |
|--|----------|
| Pin  | Function |
| 1  | Line     |
| 2  | Neutral  |

| Output Connector J2<br>6 Position<br>Molex pn. 09-65-2068 |          |
|---|----------|
| Pin   | Function |
| 1   | +V1      |
| 2   | +V1      |
| 3   | +V1      |
| 4   | RTN      |
| 5   | RTN      |
| 6   | RTN      |

| Fan Connector J3<br>Molex pn. 22-04-1021 |             |
|--|-------------|
| Pin                                      | Function    |
| 1  | Fan + (12V) |
| 2  | Fan -       |

| Signal Connector J4<br>Molex pn. B10B-PHDSS |                 |     |          |
|---|-----------------|-----|----------|
| Pin   | Function        | Pin | Function |
| 1   | +Sense          | 6   | N/C      |
| 2   | -Sense          | 7   | N/C      |
| 3   | XP Internal Use | 8   | N/C      |
| 4   | Inhibit LO      | 9   | N/C      |
| 5   | Inhibit HI      | 10  | N/C      |

### Notes:

- All dimensions in mm (inches).
- Tolerance x.xx (x.x) = 0.50 (±0.02); x.xxx (x.xx) = 0.25 (±0.01).
- Weight: 0.29kg (0.65lbs).
- 6 position single row J2 mates with Molex Housing Pn. 09-50-1061 and with Molex series 5194 crimp terminals. 12 position dual row J2 mates with Molex Housing Pn. 39-01-2125 and with Molex series 5556 crimp terminals. J3 mates with Molex Housing Pn. 51191-0200 and with Molex series 50802 crimp terminals. J4 mates with JST Housing Pn. PHDR-10VS and with JST SPHD-001T-P0.5 crimp terminals.
- The output connection options mentioned on page 7 are also available for this kind of enclosure.

## Thermal considerations

In order to ensure safe operation of the PSU in the end-use equipment, the temperature of the components listed in the table below must not be exceeded. Temperature should be monitored using K type thermocouples placed on the hottest part of the component (out of direct air flow). See below for component locations.

| Temperature measurements |                     |
|--------------------------|---------------------|
| Component                | Max. temperature °C |
| T1 Coil                  | +120°C              |
| L3 Coil                  | +120°C              |
| Q1 Body                  | +120°C              |
| Q3 Body                  | +120°C              |
| C6                       | +105°C              |
| C23                      | +105°C              |

## Service life

The estimated service life of the GCS Series is determined by the cooling arrangements and load conditions experienced in the end application. Due to the uncertain nature of the end application this estimated service life is based on the actual measured temperature of a key capacitors with in the product when installed by the end application. The worst case of the two figures should be taken as the indicative service life in 24/7 operation.

The graphs below expresses the estimated lifetime of a given component temperature and assumes continuous operation at this temperature.

### Estimated service life vs component temperature

