─ LCS75 Series



75W CONVECTION COOLED

The LCS series of regulated output convection cooled AC-DC power supplies are designed to provide a cost effective solution for industrial electronics, technology and household applications. Features include output voltage adjustment, a power 'ON' LED, low stand-by power consumption, output short circuit protection, over current and over voltage protection. Applications include auxiliary power sources, security installations, lighting control, smart home or office control systems, ticketing and vending applications.

Features

- 75W convection cooled
- ITE, industrial and household approvals
- Integrated connector cover
- Class B conducted & radiated emissions
- Input voltage range 85-264VAC
- 300VAC withstand voltage for 5s
- Output voltages from 5V to 48VDC
- Efficiency to 91%
- Short circuit, overvoltage & overload protection
- Conformal coating option
- -30°C to +70°C operating temperature
- 3 year warranty

AC-DC POWER SUPPLIES



Applications





Household

Instrumentation







Industrial Electronics

Robotics

Dimensions

3.89" x 3.82" x 1.18" (99.0 x 97.0 x 30.0 mm)

Models & Ratings

Model Number ⁽³⁾	Outp	Output Voltage		Ripple & Noise	Efficiency ⁽²⁾	Maximum	Power
Model Number	Nominal	Adjustment Range ⁽⁴⁾	Output Current	pk to pk ⁽¹⁾	Efficiency	Capacitive Load	Power
LCS75US05	5.0V	4.5 - 5.5V	14.0A	100mV	86%	10000µF	70W
LCS75US12	12.0V	10.2 - 13.8V	6.0A	120mV	88%	6000µF	72W
LCS75US15	15.0V	13.5 - 18.0V	5.0A	120mV	88%	5000µF	75W
LCS75US24	24.0V	21.6 - 28.8V	3.2A	150mV	90%	1500µF	77W
LCS75US36	36.0V	32.4 - 39.6V	2.1A	200mV	90%	1000μF	76W
LCS75US48	48.0V	43.2 - 52.8V	1.6A	200mV	91%	680µF	77W

Notes:

- $1.\ Ripple\ \&\ noise\ measured\ with\ 20MHz\ bandwidth\ and\ 47\mu F\ electrolytic\ capacitor\ in\ parallel\ with\ 0.1\mu F\ ceramic\ capacitor.$
- 2. Typical efficiencies measured at 230VAC full load.
- 3. Add suffix -E to model number to specify conformal coating option, MOQ applies, please contact sales.
- 4. Output power rating must not be exceeded.

Contract Series Contract S

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
	85	115/230	264	VAC	Derate output power linearly from 100% at 100VAC to 80% at 85VAC
Input Voltage - Operating	120		373	VDC	Alternative input. Not to be used in addition to AC input. DC input not included in safety approvals, external DC rated fuse required. Derate output power linearly from 100% at 140VDC to 80% at 120VDC
Input Frequency	47	50/60	63	Hz	
Surge Withstand	300VAC for r	300VAC for maximum 5s			
Innut Cument Full Load		2.0		Α	115VAC
Input Current - Full Load		1.0		А	230VAC
No Load Input Power			0.3	W	
l		40		^	115VAC cold start at 25°C ambient
Inrush Current		65		Α	230VAC cold start at 25°C ambient
Earth Leakage Current			0.75	mA	230VAC/50Hz (Typ)
Input Protection	T3.15A / 250	T3.15A / 250VAC Internal fuse fitted in line			

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Co	onditions
Output Voltage	5		48	VDC	See Mode	ls & Ratings table
		±2		% Full lo	Full load	LCS75US05
Initial Set Accuracy		±1		%0	Full load	All other models
Voltage Adjustment			±10	%		
Minimum Load	0			Α	No minimum load required	
Start Up Delay			300	ms	115/230VA	C full load
Hold He Time		8			115VAC	
Hold Up Time		55		ms	230VAC	
Drift			±0.03	%	After 20 m	inutes warm up, 230VAC, 0°C to 50°C
Line Regulation			±0.5	%	100-264VA	C, full load
Load Regulation			±1	% 0-100	0-100%	LCS75US05
			±0.5	%0		All other models
Transient Response			10	%	Recovery v	vithin 1% in less than 3ms for a 50-75% and 75-50% loa
Ripple & Noise				mV pk-pk	See Mode	s and Ratings table
Over/Undershoot			10	%	Full load	
			6.3		LCS75US0	05
			16.2		LCS75US1	2
			21.75	1/00	LCS75US1	
Overvoltage Protection			33.6	VDC	LCS75US2	Auto recovery
			50.0		LCS75US3	36
			60.0		LCS75US48	18
Overload Protection	110		200	%	Nominal or	utput current, auto recovery
Temperature Coefficient		±0.03		%/°C		
Short Circuit Protection			5	s	Trip and re	start, auto recovery



General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		88		%	230VAC Full load (see Models & Ratings table)
Isolation: Input to Output	4000			VAC	
Input to Ground	2000			VAC	Class I construction
Output to Ground	1250			VAC	
Switching Frequency		65		kHz	
Power Density			2.78	W/in³	
Mean Time Between Failure	300			khrs	MIL-HDBK-217F, Notice 2 +25°C GB
Weight		0.485 (220)		lb(g)	
Case Material	Aluminium chassis with vented galvanized steel cover				
Conformal Coating Option	Acrylic resin, UL94V-0 rated, certified (UL No. E351072), minimum 30µm coating thickness. Add suffix -E to part number				

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-30		+70	°C	See derating curve
Storage Temperature	-40		+85	°C	
Cooling	Natural convection				
Humidity	5		90	%RH	Non-condensing
Operating Altitude			5000	m	
Shock and Vibration	Tested according to EN60068-2-27, 10 - 500Hz, 5g (1H) for each X, Y and Z plane				

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55032	Class B	
Radiated	EN55032	Class B	
Harmonic Current	EN61000-3-2	Class A	

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD Immunity	EN61000-4-2	3	А	Contact ±6kV / Air ±8kV
Radiated Immunity	EN61000-4-3	3	Α	10V/m
EFT	EN61000-4-4	3	Α	±2kV
Surge	EN61000-4-5	Installation class 4	Α	Line to line ±2kV, line to ground ±4kV
Conducted	EN61000-4-6	3	А	10Vrms
Dips	EN61000-4-11	Dip. 100% (0VAC), 10ms Dip. 100% (0VAC), 20ms Dip. 60% (88VAC), 200ms Dip. 30% (154VAC), 500ms Dip. 20% (176VAC), 5000ms	А	
Interrupt		Int. 100% (0VAC), 5000ms	В	0%, 70%




Safety Approvals

Safety Agency	Standard	Notes & Conditions
UL	UL62368-1	Information Technology
TUV	EN62368-1, EN60335, EN61558	Information Technology and Household
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

Application Notes


Temperature Derating




Notes:

- 1. With 230VAC or 140VDC input no derating below -25°C
- 2. With input at 100VAC or 120VDC derate output power to 75%

Mechanical Details





Pin-Out			
Pin Function			
1	AC(L)		
2	AC(N)		
3			
4	-Vo		
5	+Vo		

Connector torque: M3.5, 0.8Nm

Notes:

- 1. All dimensions are in inches (mm).
- 2. Tightening torque: M3, 0.4Nm fixings
- 3. General tolerances: ±0.039 (±1.00)
- 4. Chassis must be connected to protective earth.

0

3.898 (99.0)