VR20 Series

DC-DC Converter



2 Amp

- Non Isolated 2A Switching Regulator
- Regulated Single Outputs from 2.5 to 15VDC
- Wide Input Range to 36V
- SIP3 Package
- High Efficiency to 96%
- Class B Conducted & Radiated Emissions
- Short Circuit Protection
- Low 0.1 mA Standby Input Current
- -40°C to +85°C Operation
- MTBF >2MHrs
- 3 Year Warranty

The VR20 provides a cost effective compact efficient switching regulator solution operating from a wide range DC input. Output voltages start from 2.5V and the VR20 consumes as little as 0.1mA when idle.



VR20:

0.453 x 0.689 x 0.354" (11.5 x 17.5 x 9.0mm)

Models & Ratings

	`							
Input Voltage	Output Voltage	utput Voltage Output Current		t Current ⁽¹⁾	Max. Capacitive	Efficiency ⁽²⁾		- Model Number
input voltage	Output voltage		No Load	Full Load	Load	Vin, Min.	Vin, Max.	Woder Number
4.5-36V	2.5V	2.0A	0.2mA	1300mA	2000µF	89%	83%	VR20S2V5
6.0-36V	3.3V	2.0A	0.1mA	1260mA	1800µF	89%	85%	VR20S3V3
8.0-36V	5.0V	2.0A	0.1mA	1380mA	1000µF	92%	89%	VR20S05
13-36V	9.0V	2.0A	0.1mA	1490mA	680µF	95%	92%	VR20S09
16-36V	12V	2.0A	0.1mA	1590mA	470µF	96%	94%	VR20S12
18-36V	15V	2.0A	0.1mA	1760mA	470µF	96%	94%	VR20S15

Notes


- 1. Full load input current measured at minimum input voltage.
- 2. Efficiency measured at full load.

3. Standard tube quantity 44 pcs.

4. Case & pin tolerance: ±0.02 (±0.5)

4. Right angle pin option, add suffix -RA.

Mechanical Details



Notes

- 1. All dimensions are in inches (mm)
- 2. Weight: 0.0083lbs (3.8g) approx.
- 3. Pin diameter: 0.02±0.004 (0.7±0.1)

VR20 Series



Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	4.5		36	VDC	See Models and Ratings table.
Input Filter	Internal capacitor				
Input Reflected Ripple			20	mA pk-pk	
Input Surge			45	VDC	For max. 100ms.

Output					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	2.5		15	VDC	See Models and Ratings table.
Initial Set Accuracy		±2.0	±4.0/±3.0	%	2.5V and 3.3V/others (At full load)
Minimum Load	0			mA	No minimum load required.
Line Regulation		±0.4	±0.8	%	Full load over input voltage range.
Load Regulation		±0.5	±1.5	%	Maximum variation applies to 2.5V output models.
Transient Response			±5	%	For 50% load change. Recovery in 200µs.
Ripple & Noise			75	mV pk-pk	20 MHz bandwidth.
Short Circuit Protection	Continuous, with	h auto recovery. Hi	ccup mode.	•	
Maximum Capacitive Load See Models and Ratings table.		l Ratings table.			
Temperature Coefficient			0.03	%/°C	
Overload Protection		3.5		A	
Start-up Time		20		ms	

General							
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions		
Efficiency			96	%	See models and ratings table.		
Isolation: Input to Output	0			VDC	Non isolated.		
Switching Frequency		400		kHz	At full load.		
Mean Time Between Failure	2			MHrs	MIL-HDBK-217F.		
Weight		0.0083 (3.8)		lb (g)			
Case Material	Non-conductive	Non-conductive black plastic UL94V-0.					
Pin Material	Solder coated p	Solder coated phosphor bronze C5191R-1/2H.					
Potting Material	Polyurethane typ	oe L780 UL94V-0 r	ated.				
Water Wash	Use de-ionised water only, dry thoroughly.						
Soldering Temperature			260	°C	Wave solder peak, 1.5mm from case 10s max. Not suitable for vapour phase soldering. For further details contact XP Power applications team.		

Environmental					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-40		+85	°C	See derating curves.
Storage Temperature	-55		+125	°C	
Case Temperature			+120	°C	
Humidity			95	%RH	Non-condensing.
Cooling	Natural convectio	on.			

VR20 Series

DC-DC Converter

EMC: Emissions


Phenomenon	Standard	Test Level	Notes & Conditions	
Conducted	EN55032	Class B	See Application Notes	
Radiated	EN55032	Class B	See Application Notes	

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD Immunity	EN61000-4-2	±6kV	В	Contact discharge.
Radiated Immunity	EN61000-4-3	10V/m	A	
EFT/Burst	EN61000-4-4	±1.0kV	В	See Application Notes
Surges	EN61000-4-5	±1.0kV	В	See Application Notes
Conducted Immunity	EN61000-4-6	3Vrms	A	

Application Notes

Input Filter to meet Class B Conducted Emissions




L	C1	C2/C3	C4	C5
22µH	100µF/100V	10µF/50V	680µF/50V	22µF/25V

XP Power


Select fuse rating based on application input current.


Typical Application



Part Number	C6	C7	
VR20S2V5		22µF/10V	
VR20S3V3		22µF/10V	
VR20S05	22µF/50V	22µF/10V	
VR20S09	22μ1/300	22µF/16V	
VR20S12]	22µF/25V	
VR20S15		22µF/25V	

Derating Curves





www.xppower.com