

# CERTIFICATE OF COMPLIANCE

**Certificate Number** 20190404-E317867  
**Report Reference** E317867-A57-UL  
**Issue Date** 2019-APRIL-04

**Issued to:** XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780

**This certificate confirms that  
representative samples of**

COMPONENT - POWER SUPPLIES, INFORMATION  
TECHNOLOGY EQUIPMENT INCLUDING ELECTRICAL  
BUSINESS EQUIPMENT; COMPONENT - POWER  
SUPPLIES FOR USE WITH AUDIO/VIDEO,  
INFORMATION AND COMMUNICATION TECHNOLOGY  
EQUIPMENT

See addendum page

Have been investigated by UL in accordance with the  
component requirements in the Standard(s) indicated on  
this Certificate. UL Recognized components are incomplete  
in certain constructional features or restricted in  
performance capabilities and are intended for installation in  
complete equipment submitted for investigation to UL LLC.

**Standard(s) for Safety:** See addendum page

**Additional Information:** See the UL Online Certifications Directory at  
<https://iq.ulprospector.com> for additional information.

This *Certificate of Compliance* does not provide authorization to apply the UL Recognized Component Mark. Only the UL Follow-Up Services Procedure provides authorization to apply the UL Mark.

Only those products bearing the UL Recognized Component Mark should be considered as being UL Certified and covered under UL's Follow-Up Services.

Look for the UL Recognized Component Mark on the product.



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



# CERTIFICATE OF COMPLIANCE

**Certificate Number** 20190404-E317867  
**Report Reference** E317867-A57-UL  
**Issue Date** 2019-APRIL-04

This is to certify that representative samples of the product as specified on this certificate were tested according to the current UL requirements.

## Products

Switching Power Supply

Model - ECL15XXYY-Z

Where XX is UD or UT, YY is 01, 02 or 03, Z is P, T, E, S, SD or blank.

## Standards

UL 60950-1, Information Technology Equipment - Safety - Part 1: General Requirements

CAN/CSA C22.2 No. 60950-1-07, Information Technology Equipment - Safety - Part 1: General Requirements



Bruce Mahrenholz, Director North American Certification Program

UL LLC

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL. For questions, please contact a local UL Customer Service Representative at <http://ul.com/aboutul/locations/>



## UL TEST REPORT AND PROCEDURE

<b>Standard:</b>	UL 60950-1, 2nd Edition, 2014-10-14 (Information Technology Equipment - Safety - Part 1: General Requirements) CAN/CSA C22.2 No. 60950-1-07, 2nd Edition, 2014-10 (Information Technology Equipment - Safety - Part 1: General Requirements)
<b>Certification Type:</b>	Component Recognition
<b>CCN:</b>	QQGQ2, QQGQ8 (Power Supplies for Information Technology Equipment Including Electrical Business Equipment)
<b>Complementary CCN:</b>	QQJQ2, QQJQ8 (Power Supplies for Use in Audio/Video, Information and Communication Technology Equipment)
<b>Product:</b>	Switching Power Supply
<b>Model:</b>	ECL15XXYY-Z  Where XX is UD or UT, YY is 01, 02 or 03, Z is P, T, E, S, SD or blank.
<b>Rating:</b>	INPUT: 100-240V~ 0.3 A, 50/60 Hz  Output: See Model Differences section.
<b>Applicant Name and Address:</b>	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES

This is to certify that representative samples of the products covered by this Test Report have been investigated in accordance with the above referenced Standards. The products have been found to comply with the requirements covering the category and the products are judged to be eligible for Follow-Up Service under the indicated Test Procedure. The manufacturer is authorized to use the UL Mark on such products which comply with this Test Report and any other applicable requirements of UL LLC ('UL') in accordance with the Follow-Up Service Agreement. Only those products which properly bear the UL Mark are considered as being covered by UL's Follow-Up Service under the indicated Test Procedure.

The applicant is authorized to reproduce the referenced Test Report provided it is reproduced in its entirety.

UL authorizes the applicant to reproduce the latest pages of the referenced Test Report consisting of the first page of the Specific Technical Criteria through to the end of the Conditions of Acceptability.

Any information and documentation involving UL Mark services are provided on behalf of UL LLC (UL) or any authorized licensee of UL.

Prepared by: Adam Tangocci / Project Handler

Reviewed by: Gregory Ray / Reviewer

### Supporting Documentation

The following documents located at the beginning of this Procedure supplement the requirements of this Test Report:

- A. Authorization - The Authorization page may include additional Factory Identification Code markings.
- B. Generic Inspection Instructions -
  - i. Part AC details important information which may be applicable to products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of this Test Report.
  - ii. Part AE details any requirements which may be applicable to all products covered by this Procedure. Products described in this Test Report must comply with any applicable items listed unless otherwise stated in the body of each Test Report.
  - iii. Part AF details the requirements for the UL Certification Mark which is not controlled by the technical standard used to investigate these products. Products are permitted to bear only the Certification Mark(s) corresponding to the countries for which it is certified, as indicated in each Test Report.

### Product Description

The unit is a switching type power supply in which electronic components are mounted on PWB for installing to Information Technology Equipment (ITE).

### Model Differences

Models listed are identical except minor differences in transformer secondary winding turns, some components to regulate output voltage and current. (Denoting non-safety related differences.)

Suffix definition - Z can be P, T, E, S or SD. P means open frame PCB mount, T means open frame Chassis mount, E means with enclosure and encapsulated, S means screw terminal mounted on the enclosure and SD means DIN rail mounted on the enclosure.

Model ECL15XXYY-T is similar to ECL15XXYY-P except for ECL15XXYY-T has I/O connectors and ECL15XXYY-P has I/O pins.

Model ECL15XXYY-P is similar to Model ECL15XXYY-E except for ECL15XXYY-E is housed in plastic enclosure with epoxy.

Model ECL15XXYY-S is similar to Model ECL15XXYY-E except for Model ECL15XXYY-S with I/O terminal blocks, ECL15XXYY-E with I/O pins, enclosure shape, PWB layout and model designation.

Model ECL15XXYY-SD is similar to Model ECL15XXYY-S except for Model ECL15XXYY-SD is provided with a DIN rail clip.

#### Output Ratings:

ECL15UD01-Z  
V1: 12.0 Vdc, 0.65A  
V2: 12.0 Vdc, 0.65A

ECL15UD02-Z  
V1: 15.0 Vdc, 0.5A  
V2: 15.0 Vdc, 0.5A

ECL15UD03-Z  
V1: 5.0 Vdc, 2.0A  
V2: 12.46 Vdc, 0.625A

ECL15UT02-Z  
V1: 5.0 Vdc, 2.0A  
V2: 11.9 Vdc, 0.2A  
V3: 11.9 Vdc, 0.2A

ECL15UT03-Z  
V1: 5.0 Vdc, 2.0A  
V2: 15.5 Vdc, 0.15A  
V3: 15.5 Vdc, 0.15A

### Technical Considerations

- Equipment mobility : movable
- Connection to the mains : not directly connected to the mains
- Operating condition : continuous
- Access location : for building-in
- Over voltage category (OVC) : OVC II
- Mains supply tolerance (%) or absolute mains supply values : +10%, -10% (manufacturer declared)
- Tested for IT power systems : No
- IT testing, phase-phase voltage (V) : N/A
- Class of equipment : Class I or Class II (Determined by end product)
- Considered current rating of protective device as part of the building installation (A) : 20 A
- Pollution degree (PD) : PD 2
- IP protection class : IP X0
- Altitude of operation (m) : up to 3048 m
- Altitude of test laboratory (m) : 180 m
- Mass of equipment (kg) : < 0.1 kg
- The product was submitted and evaluated for use at the maximum ambient temperature (T<sub>ma</sub>) permitted by the manufacturer's specification of: 50 degree C (100% full load) and 70 degree C (50% full load)
- The product is intended for use on the following power systems: TN
- The means of connection to the mains supply is: to be considered in end product. (Building-in component)
- The equipment disconnect device is considered to be: provided in end system. (Building-in component)
- The following accessible locations (with circuit/schematic designation) are within a limited current circuit: After CY1
- The following circuit locations (with circuit/schematic designation) were investigated as a limited power source (LPS): Secondary output
- The product was investigated to the following additional standards: EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011 + A2:2013 (which includes all European national differences, including those specified in this test report).
- According to IEC60664-1, Table A2, required Clearances have been adjusted by multiplying the clearance at sea level by a factor of 1.15 for operating at an altitude of 3048 meters. The correction factor is based on barometric pressure of 70kPa and Overvoltage Category II. If the calculated

Clearance exceeded the Creepage, the Creepage was adjusted to the value of clearance.

### Engineering Conditions of Acceptability

For use only in or with complete equipment where the acceptability of the combination is determined by UL LLC. When installed in an end-product, consideration must be given to the following:

- Secondary circuits are isolated from primary circuits by double or reinforced insulation, however the Class of equipment shall be considered in the end product.
- Terminal block type ELK508 series suitable for solid/stranded copper wiring only, 30-14 AWG, 4.5 lbs.-in. torque. Terminal block type ETB33 series suitable for solid/stranded copper wiring only, 22-14 AWG, 3.48 lbs.-in. torque.
- The following Production-Line tests are conducted for this product: Electric Strength
- The end-product Electric Strength Test is to be based upon a maximum working voltage of: Primary-SELV: 252 Vrms, 651 Vpk
- The following secondary output circuits are SELV: Secondary output
- The following secondary output circuits are at non-hazardous energy levels: Secondary output
- The following secondary output circuits are Limited Current Circuits: After CY1
- The following secondary output circuits are supplied by a Limited Power Source: Secondary Output
- The power supply terminals and/or connectors are: Not investigated for field wiring except terminal block ETB33, ELK508, ELK508S for cULus only.
- The maximum investigated branch circuit rating is: 20 A
- The investigated Pollution Degree is: 2
- The following magnetic devices (e.g. transformers or inductor) are provided with an OBJY2 insulation system with the indicated rating greater than Class 105(A): Transformer T1 - Class 130(B)
- The following end-product enclosures are required: Mechanical, Fire, Electrical
- The clearance and creepage distances have additionally been assessed for suitability up to 3048 m elevation, except for China (up to 2000 m elevation).
- Printed Wiring Board rated 130°C.

### Additional Information

This report is a Standard upgrade/reissue of CBTR Ref. No.: E317867-A57-CB-1, CB Test Certificate Ref. No. US-17793-UL, US-17793-A1-UL, and US-17793-A2-UL to IEC 60950-1:2005 (Second Edition), Am1:2009 + Am2:2013. Based on the previously conducted testing and the review of product technical documentation including photos, schematics, wiring diagrams and similar, only the construction review and the review of previous tests was deemed necessary. All required tests were carried out under the original investigation.

In addition, an alternate label system was added to this report (3M, Types 7816 or 7818) based on previous evaluation for this manufacturer under CBTR Ref. No.: E139109-A139, CBTC Ref. No.: US- 24981-UL and US-24981-M1-UL.

The clearance and creepage distances have additionally been assessed for suitability up to 3048 m elevation.

A warning label with the wording "use only in non-tropical climate conditions" will be located on the unit.

The marking plate is considered being representative of all models in all series covered by this report.

Technical Amendment:

- Models and ratings sections were updated for clarity.
- Output ratings enclosure document removed and output ratings information added to Model Differences section.
- Temperature Table replaced with correct data.
- UL: Bleeder resistors were updated for 60950 and 62368 in the critical components table.
- UL: The manufacturer submitted representative production samples of these models for construction review and testing. Evaluation and testing were performed for compliance to UL 62368-1 Edition 2 and CSA C22.2 NO. 62368-1-14 - Edition 2. Evaluation specifics can be found under CBTR E317867-A6042-CB-1.

**Additional Standards**

The product fulfills the requirements of: EN 60950-1:2006 + A1:2010 + A11:2009 + A12:2011 + A2:2013, CSA C22.2 No. 60950-1-07 2nd Ed. Revised 2014-10-14, IEC 60950-1:2005 + A1:2009 + A2:2013, UL 60950-1 2nd Ed. Revised 2014-10-14

**Markings and instructions**

Clause Title	Marking or Instruction Details
1.7.1 Power rating - Ratings	Ratings (voltage, frequency/dc, current)
1.7.1 Power rating - Company identification	Listee's or Recognized company's name, Trade Name, Trademark or File Number
1.7.1 Power rating - Model	Model Number
1.7.6 Fuses - Non-operator access/soldered-in fuses	Unambiguous reference to service documentation for instructions for replacement of fuses replaceable only by service personnel

**Special Instructions to UL Representative**

Inspect the transformer(s) listed in BD1.1 per AA1.1- (C). When the tests are conducted at other location, inspect test record and specification sheet provided by the component manufacturer. Verify the specification sheet indicates 100% routine test specified in BD1.1 be conducted at the component manufacturer.

<b>Production-Line Testing Requirements</b>						
<b><u>Electric Strength Test Special Constructions - Refer to Generic Inspection Instructions, Part AC for further information.</u></b>						
Model	Component	Removable Parts	Test probe location	V rms	V dc	Test Time, s
All models	T1	--	T1 Pri. to Sec.	300 0V	4200	1s
<b><u>Earthing Continuity Test Exemptions - This test is not required for the following models:</u></b>						
All models						
<b><u>Electric Strength Test Exemptions - This test is not required for the following models:</u></b>						
--						
<b><u>Electric Strength Test Component Exemptions - The following solid-state components may be disconnected from the remainder of the circuitry during the performance of this test:</u></b>						
--						
<b><u>Sample and Test Specifics for Follow-Up Tests at UL</u></b>						
Model	Component	Material	Test	Sample(s)	Test Specifics	
--	--	--	--	--	--	