



QQGQ2.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

XP POWER L L C

E317867

15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

	Rated Input			Max Output							
Model No.	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
"Switching Power Supply".											
ECE60USXX (where XX can be any number between 3 and 48 designating the output voltage), may also be provided with suffix "S" and/or "D", "-" provided optionally											
	100-240ac	50-60	0	3.3dc	10	33	3	60950-1, 2nd Ed+AM1+AM2	20B	0	2
				5dc	10	50	3				
				9dc	6.67	60	3				
				12dc	5	60	3				
				15dc	4	60	3				
				24dc	2.5	60	3				
				36dc	1.67	60	3				
				48dc	1.25	60	3				
ECL15UD01-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	-12dc	0.65	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.65	-	3				
ECL15UD02-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	15dc	0.5	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				-15dc	0.5	-	3				
ECL15UD03-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.625	-	3				
ECL15UT02-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.2	-	3				
				-12dc	0.2	-	3				
ECL15UT03-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd	20B	0	1

[illegible]

	5	-	3	15dc	0.2	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0305S3V3[*r]											
	5dc	-	3	3.3dc	600	1.98	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0312D05[*r]											
	12dc	-	3	+5dc	+0.3	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-5dc	-0.3	1.5	3				
IEU0312D12[*r]											
	12dc	-	3	+12dc	+0.125	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-12dc	-0.125	1.5	3				
IEU0312D15[*r]											
	12dc	-	3	+15dc	+0.1	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-15dc	-0.1	1.5	3				
IEU0312S05[*r]											
	12dc	-	3	5dc	0.6	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0312S12[*r]											
	12dc	-	3	12dc	0.25	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0312S15[*r]											
	12dc	-	3	15dc	0.2	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0312S3V3[*r]											
	12dc	-	3	3.3dc	0.6	1.98	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0324D05[*r]											
	24dc	-	3	+5dc	+0.3	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-5dc	-0.3	1.5	3				
IEU0324D12[*r]											
	24dc	-	3	+12dc	+0.125	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-12dc	-0.125	1.5	3				
IEU0324D15[*r]											
	24dc	-	3	+15dc	+0.1	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-15dc	-0.1	1.5	3				
IEU0324S05[*r]											
	24dc	-	3	5dc	0.6	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0324S12[*r]											
	24dc	-	3	12dc	0.25	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0324S15[*r]											
	24dc	-	3	15dc	0.2	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0324S3V3[*r]											

	24dc	-	3	3.3dc	0.6	1.98	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0348D05[*r]											
	48dc	-	3	+5dc	+0.3	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-5dc	-0.3	1.5	3				
IEU0348D12[*r]											
	48dc	-	3	+12dc	+0.125	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-12dc	-0.125	1.5	3				
IEU0348D15[*r]											
	48dc	-	3	+15dc	+0.1	1.5	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
				-15dc	-0.1	1.5	3				
IEU0348S05[*r]											
	48dc	-	3	5dc	0.6	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0348S12[*r]											
	48dc	-	3	12dc	0.25	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0348S15[*r]											
	48dc	-	3	15dc	0.2	3	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IEU0348S3V3[*r]											
	48dc	-	3	3.3dc	0.6	1.98	3	60950-1, 2nd Ed+AM1+AM2	--	0	0
IFC125-10[*r]											
	100-240ac	50-60	0	5	25	125	3	60950-1	-	0	0
				12	0.5	6	3				
IFC125-12[*r]											
	100-240ac	50-60	0	12	10.5	125	3	60950-1	-	0	0
				12	0.5	-	3				
IFC125-13[*r]											
	100-240ac	50-60	0	15	8.3	125	3	60950-1	-	0	0
				12	0.5	-	3				
IFC125-14[*r]											
	100-240ac	50-60	0	24	5.2	125	3	60950-1	-	0	0
				12	0.5	-	3				
IFC125-18[*r]											
	100-240ac	50-60	0	48	2.6	125	3	60950-1	-	0	0
				12	0.5	-	3				
IFC125-31[*r]											
	100-240ac	50-60	0	5	16.5	125	3	60950-1	-	0	0
				12	5	-	3				
				-12	0.5	-	3				
IFC125-40-1[*r]											
	100-240ac	50-60	0	2.5	12	125	3	60950-1	-	0	0

				41dc	11.29	350	3				
XP0501x-48 (j)											
	100-240ac	47-63	0	53dc	5.47	230	3	60950-1	20B	2	1
				53dc	8.33	350	3				
XP0501x-54 (j)											
	100-240ac	47-63	0	60dc	4.25	230	3	60950-1	20B	2	1
				60dc	6.48	350	3				
ZAB05US24											
	100-240ac	50/60	0	24.14dc	0.3	7.1	3	60950-1, 2nd Ed+AM1+AM2	20B	0	2

[*r] - Output values are rated.

- Represents 0-9.

(#) - where X can be any number between 03 and 48

(&) - input range from -36 to -72 Vdc (+/- 0% tolerance)

(-P) - May be followed by suffix P.

(1) - [#] where Y= B or C

(2) - [+] where X= 05,12,15,24,30,48

(a) - Where Y = T, P, E, S or SD

(a1) - X can be any alphanumeric or blank

(AA) - Where XX can be any number between 3 and 48 designating the output voltage

(AB) - May also be provided with suffix "S" and/or "D", "-" provided optionally

(b) - z=blank, 0-9 , A-Z

(bb) - Rating B output max 155 W

(c1) - followed by C, CD, CL, or CDL

(c2) - followed by E, ED, EL, or EDL

(c3) - followed by F, FD, FL, or FDL

(c4) - Rating B output max 155 W

(cc) - Where xx can be alphanumeric or blank for marketing purposes only.

(d) - Denotes that other output voltages are available for the series; tested voltages noted only.

(gg) - 1st * = S, D, T or Q; 2nd to 3rd * = 00-48; 4th * = B, C, D or blank; 5th * = -C or blank

(h) - May be followed by suffix L

(i) - X may be - or blank; Y may be C, D, E, F or blank; Z may be B, D F or blank

(i1) - For input=100-130Vac

(i2) - For input=130-240Vac

(j) - x may blank or F

(k) - y may be Blank (without fan) or A (u-case + top cover)

(l) - y is Blank (without fan)

(m) - y is A (with fan)

(n) - y is C (for Enclosure)

(o) - y may be R, S or T

(p) - z may be A-Z, a-z, 0-9 or blank

(q) - output represents rated voltage

(r) - Values for max. V and max. A are output ratings

(s) - * may be blank, B or P; # may be blank or P

(t) - Y can be E, P, T or S; Z can be 0-9, A-Z or a-z

(u) - xxx will be 03 through 480 inclusively

(v) - 4.99 Volt output is for model CU20-10; 24 Volt output is for model CU20-14; 15.87 Volt output is for model CU20-16