



Product Service

CERTIFICATE

No. B 057396 0511 Rev. 00

Model(s): HPT5K0TSxxx Series
(where x can be 0 to 9 which represents rated output voltage)

Brand Name: XP



Parameters:

Rated Input: 200-480 VAC, 3-Phase (3W+PE)

Rated Current: 10 A Max Per Phase

Rated Input Frequency: 50/60 Hz

Elevation for Use: 0-5000 m above sea level

Protection Class: Class I at end use

Maximum Temperature, Ambient: 50°C with 100% of rated output, 70°C with 50% of rated output

Rated Outputs:

Model Number	OUTPUT RATING				
	Voltage (VDC)	200-240 V ac input range		380-480 Vac input range	
		Max Current (A)	Max Power (W)	Max Current (A)	Max Power (W)
HPT5K0TS060	0-60	50	3000	83.33	5000
HPT5K0TS100	0-100	30	3000	50	5000
HPT5K0TS200	0-200	15	3000	25	5000

All models are provided with an isolated 5Vdc/2 A output. De-rated by percentage same as conditions noted above for main output.

ZERTIFIKAT • CERTIFICATE • 認證證書 • CERTIFICADO • CERTIFICAT

