




Ref. Certif. No.

US-32385-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	DC/DC Converters
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 USA
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 USA
Name and address of the factory	XP POWER L L C 2436 PRECISION DRIVE MINDEN NV 89423 USA
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	INPUT: 5 VDC, 550 mA; 12 VDC, 250 mA; 24 VDC, 120 mA Ratings Optional. See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	A Series, AG Series, AGH Series, AH Series See Page 2
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report. <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6034-CB-2 issued on 2018-08-31

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-12-06
Original Issue Date: 2018-08-31

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32385-A1-UL

Model Details:

A Series, Models A01, A02, A025, A03, A04, A05, A06, A07, A08, A09, A10, A12, A15, A20, A30, A40, A50 and A60, maybe followed by suffix T, maybe followed by suffix R to indicate compliance with EU RoHS requirements.

AH Series, Models AH01, AH02, AH025, AH03, AH04, AH05, AH06, AH07, AH08, AH09, AH10, AH12, AH15, AH20, AH30 and AH60, maybe followed by suffix T, maybe followed by suffix R to indicate compliance with EU RoHS requirements..

AG Series, Models AG01, AG02, AG025, AG03, AG04, AG05, AG06, AG07, AG08, AG09, AG10, AG12, AG15, AG20, AG30, AG40, AG50 and AG60, maybe followed by suffix T, maybe followed by suffix R to indicate compliance with EU RoHS requirements..

AGH Series, Models AGH01, AGH02, AGH025, AGH03, AGH04, AGH05, AGH06, AGH07, AGH08, AGH09, AGH10, AGH12, AGH15, AGH20, AGH30 and AGH60 maybe followed by suffix T, maybe followed by suffix R to indicate compliance with EU RoHS requirements.

Factories:

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215320
CHINA

Ratings:

OUTPUT: 0 to 6000 VDC.

See Enclosure - Miscellaneous 7-01 and 7-02 in Test Report for current ratings of each model.

Ratings optional.

Additional Information:

NOTE: This is a correction to the Cover Page of CB Test Certificate US-32385-UL, to include the correct Product description. The CB Test Report was not affected by this correction to the CB Test Certificate.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-12-06

Original Issue Date: 2018-08-31

Signature:

Jolanta M. Wroblewska