



QQGQ2.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

Page Bottom

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

XP POWER L L C

E317867

15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

	Rated Input			Max Output							
Model No.	Volts	Hz	SC	V	A	VA	OC	SP	EP	FC	GC
"Switching Power Supply".											
ECE60USXX (where XX can be any number between 3 and 48 designating the output voltage), may also be provided with suffix "S" and/or "D", "-" provided optionally											
	100-240ac	50-60	0	3.3dc	10	33	3	60950-1, 2nd Ed+AM1+AM2	20B	0	2
				5dc	10	50	3				
				9dc	6.67	60	3				
				12dc	5	60	3				
				15dc	4	60	3				
				24dc	2.5	60	3				
				36dc	1.67	60	3				
				48dc	1.25	60	3				
ECL15UD01-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	-12dc	0.65	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.65	-	3				
ECL15UD02-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	15dc	0.5	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				-15dc	0.5	-	3				
ECL15UD03-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.625	-	3				
ECL15UT02-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd Ed+AM1+AM2	20B	0	1
				12dc	0.2	-	3				
				-12dc	0.2	-	3				
ECL15UT03-Z (Z can be P, T, E, S, SD)[*r]											
	100-240ac	50/60	0	5dc	2.0	-	3	60950-1, 2nd	20B	0	1

	18-36dc	-	4	12.03dc	59.13	583.26	3	60950-1	40T	0	0
QSB60024S24[*r]											
	18-36 Vdc	-	4	24dc	25	600	3	60950-1 2nd	40T	0	0
QSB60024S28Z[*r]											
	18-36dc	-	4	28dc	21.5	-	3	60950-1	40T	0	0
QSB60024S32Z											
	18-36dc	-	4	32.14dc	28.44	798.31	3	60950-1	40T	0	0
QSB60024S48											
	18-36 Vdc	-	4	48.04dc	15.5	742.3	3	60950-1 2nd	40T	0	0
QSB60048S12Z[*r]											
	36-75dc	-	4	12dc	50	-	3	60950-1	40T	0	0
QSB60048S24[*r]											
	36-75 Vdc	-	4	24dc	25	600	3	60950-1 2nd	40T	0	0
QSB60048S28Z[*r]											
	18-36dc	-	4	28dc	21.5	-	3	60950-1	40T	0	0
QSB60048S32Z[*r]											
	36-75dc	-	4	32dc	19	-	3	60950-1	40T	0	0
QSB60048S48											
	36-75 Vdc	-	4	48.2dc	14.95	714.1	3	60950-1 2nd	40T	0	0
QSB7524S05, QSB7524S05N											
	9-36, 24dc	-	4	-	15.31	75.2	4	60950-1, 2nd	15T	0	0
QSB7524S12, QSB7524S12N											
	9-36, 24dc	-	4	-	7.8	93.03	4	60950-1, 2nd	15T	0	0
QSB7524S15, QSB7524S15N[*r]											
	9-36, 24dc	-	4	-	5	-	4	60950-1, 2nd	15T	0	0
QSB7524S24, QSB7524S24N											
	9-36, 24dc	-	4	-	3.75	88.8	4	60950-1, 2nd	15T	0	0
QSB7524S3V3, QSB7524S3V3N[*r]											
	9-36, 24dc	-	4	-	12	-	4	60950-1, 2nd	15T	0	0
QSB7548S05, QSB7548S05N											
	18-75, 48dc	-	4	-	14.95	73.46	4	60950-1, 2nd	8T	0	0
QSB7548S12, QSB7548S12N											
	18-75, 48dc	-	4	-	7.75	91.95	4	60950-1, 2nd	8T	0	0
QSB7548S15, QSB7548S15N[*r]											
	18-75, 48dc	-	4	-	5	-	4	60950-1, 2nd	8T	0	0
QSB7548S24, QSB7548S24N											
	18-75, 48dc	-	4	-	3.8	90.77	4	60950-1, 2nd	8T	0	0
QSB7548S3V3, QSB7548S3V3N[*r]											
	18-75, 48dc	-	4	-	12	-	4	60950-1, 2nd	8T	0	0
RCQ50110S05, RCQ50110S05-HK[*r]											
	110dc	-	2	5dc	10	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ50110S12, RCQ50110S12-HK[*r]											
	110dc	-	2	12dc	4.17	50	3	60950-1, 2nd Ed + AM1	*	0	0

RCQ50110S15, RCQ50110S15-HK[*r]											
	110dc	-	2	15dc	3.33	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ50110S24, RCQ50110S24-HK[*r]											
	110dc	-	2	24dc	2.08	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ5072S05, RCQ5072S05-HK[*r]											
	72dc	-	2	5dc	10	50	-	60950-1, 2nd Ed + AM1	*	0	0
RCQ5072S12, RCQ5072S12-HK[*r]											
	72dc	-	2	12dc	4.17	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ5072S15, RCQ5072S15-HK[*r]											
	72dc	-	2	15dc	3.33	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ5072S24, RCQ5072S24-HK[*r]											
	72dc	-	2	24dc	2.08	50	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ75110S05, RCQ75110S05-HK[*r]											
	110dc	-	2	5dc	15	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ75110S12, RCQ75110S12-HK[*r]											
	110dc	-	2	12dc	6.25	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ75110S15, RCQ75110S15-HK[*r]											
	110dc	-	2	15dc	5.0	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ75110S24, RCQ75110S24-HK[*r]											
	110dc	-	2	24dc	3.125	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ7572S05, RCQ7572S05-HK[*r]											
	72dc	-	2	5dc	15	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ7572S12, RCQ7572S12-HK[*r]											
	72dc	-	2	12dc	6.25	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ7572S15, RCQ7572S15-HK[*r]											
	72dc	-	2	15dc	5.0	75	3	60950-1, 2nd Ed + AM1	*	0	0
RCQ7572S24, RCQ7572S24-HK[*r]											
	72dc	-	2	24dc	3.125	75	3	60950-1, 2nd Ed + AM1	*	0	0
RDQ100110S05											
	66-160 or 100dc	-	4	-	27.4	134.3	3	60950-1, 2nd	2.5T	0	0
RDQ100110S05N											
	66-160 or 100dc	-	4	-	27.4	134.3	3	60950-1, 2nd	2.5T	0	0
RDQ100110S12											
	66-160 or 100dc	-	4	-	13.72	163.8	3	60950-1, 2nd	2.5T	0	0
RDQ100110S12N											

				41dc	11.29	350	3				
XP0501x-48 (j)											
	100-240ac	47-63	0	53dc	5.47	230	3	60950-1	20B	2	1
				53dc	8.33	350	3				
XP0501x-54 (j)											
	100-240ac	47-63	0	60dc	4.25	230	3	60950-1	20B	2	1
				60dc	6.48	350	3				
ZAB05US24											
	100-240ac	50/60	0	24.14dc	0.3	7.1	3	60950-1, 2nd Ed+AM1+AM2	20B	0	2

[*r] - Output values are rated.

- Represents 0-9.

(#) - where X can be any number between 03 and 48

(&) - input range from -36 to -72 Vdc (+/- 0% tolerance)

(-P) - May be followed by suffix P.

(1) - [#] where Y= B or C

(2) - [+] where X= 05,12,15,24,30,48

(a) - Where Y = T, P, E, S or SD

(a1) - X can be any alphanumeric or blank

(AA) - Where XX can be any number between 3 and 48 designating the output voltage

(AB) - May also be provided with suffix "S" and/or "D", "-" provided optionally

(b) - z=blank, 0-9 , A-Z

(bb) - Rating B output max 155 W

(c1) - followed by C, CD, CL, or CDL

(c2) - followed by E, ED, EL, or EDL

(c3) - followed by F, FD, FL, or FDL

(c4) - Rating B output max 155 W

(cc) - Where xx can be alphanumeric or blank for marketing purposes only.

(d) - Denotes that other output voltages are available for the series; tested voltages noted only.

(gg) - 1st * = S, D, T or Q; 2nd to 3rd * = 00-48; 4th * = B, C, D or blank; 5th * = -C or blank

(h) - May be followed by suffix L

(i) - X may be - or blank; Y may be C, D, E, F or blank; Z may be B, D F or blank

(i1) - For input=100-130Vac

(i2) - For input=130-240Vac

(j) - x may blank or F

(k) - y may be Blank (without fan) or A (u-case + top cover)

(l) - y is Blank (without fan)

(m) - y is A (with fan)

(n) - y is C (for Enclosure)

(o) - y may be R, S or T

(p) - z may be A-Z, a-z, 0-9 or blank

(q) - output represents rated voltage

(r) - Values for max. V and max. A are output ratings

(s) - * may be blank, B or P; # may be blank or P

(t) - Y can be E, P, T or S; Z can be 0-9, A-Z or a-z

(u) - xxx will be 03 through 480 inclusively

(v) - 4.99 Volt output is for model CU20-10; 24 Volt output is for model CU20-14; 15.87 Volt output is for model CU20-16

(^) - where y can be blank, 0-9 or A -Z for marketing purposes.

* - Where X may be F or S; Y may be P or S; Z may be A or B

@ - Where Y can be E, P, T or S. [@] - Where x represents either blank or ?-?

w - where w can be H or blank.

X - X=05, 10 or 18

Y - Y=05, 12, 15 or 24

y = - z may be blank, 0-9 or A-Z for marketing use

Z - can be N or blank, zz = 0-9, A-Z or blank

[#] - X can be either P or U

[\$] - Where y represents either blank or C

[*r] - Output values are rated.

[++++] - Where xx can be alphanumeric or blank for marketing purposes only; yy can be 12, 15, 24, 30, 36, 48, 60 to represents output voltage.

[+] - YY may be any alphanumeric character or blank

[x] - X may be 10, 12, 13, 13-1, 14, 16, 17, 18, 23, 24, 25, 30, 31, 32, 33, 40, 41, 42, 44, 45; Z may be A-Z or Blank



Marking: Company name or trademark and model designation on the product or on the smallest unit container in which the product is packaged.

Last Updated on 2016-01-19

[Questions?](#)[Print this page](#)[Terms of Use](#)[Page Top](#)

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2016 UL LLC".