



QQGQ2.E317867

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[Page Bottom](#)

Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component

[See General Information for Power Supplies, Information Technology Equipment Including Electrical Business Equipment - Component](#)

XP POWER L L C

E317867

15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

Model No.	Rated Input			Max Output				OC	SP	EP	FC	GC
	Volts	Hz	SC	V	A	VA						
"Switching Power Supply".												
ECE60USXX (where XX can be any number between 3 and 48 designating the output voltage), may also be provided with suffix "S" and/or "D", "-" provided optionally												
	100-240ac	50-60	0	3.3dc	10	33	3	60950-1, 2nd Ed + AM1	20B	0	2	
				5dc	10	50	3					
				9dc	6.67	60	3					
				12dc	5	60	3					
				15dc	4	60	3					
				24dc	2.5	60	3					
				36dc	1.67	60	3					
				48dc	1.25	60	3					
ECL15UD01-Z (Z can be P, T, E, S, SD)[*r]												
	100-240ac	50/60	0	-12dc	0.65	-	3	60950-1	20B	0	1	
				12dc	0.65	-	3					

	200-240ac	47-63	0	48-56dc	16.66	800	3	60950-1	20B	0	1
SMD800Ps60-zzz (i), SMC800Ps60-zzz (i) [*r]											
	200-240ac	47-63	0	55-60dc	14.55	800	3	60950-1	20B	0	1
SMH600PD0512-EFx-z, SMH600PD0512-TFx-z, SMH600PD0512x-z											
	100-240ac	47-63	0	5.115dc	82.55	381.37	3	60950-1, 2nd Ed + AM1	20B	0	1
				11.92dc	54.42	597.03	3				
SMH600PD0524-EFx-z, SMH600PD0524-TFx-z, SMH600PD0524x-z [*r]											
	100-240ac	47-63	0	+5Vdc	50	Total 500	3	60950-1, 2nd Ed + AM1	20B	0	1
				+24Vdc	16.67	Total 500	3				
SMH600PD1224-EFx-z, SMH600PD1224-TFx-z, SMH600PD1224x-z											
	100-240ac	47-63	0	24.30dc	27.86	653.24	3	60950-1, 2nd Ed + AM1	20B	0	1
				11.99dc	53.39	599.53	3				
SMH600PS03-EFx-z, SMH600PS04-EFx-z, SMH600PS05-EFx-z, SMH600PS03-TFx-z, SMH600PS04-TFx-z, SMH600PS05-TFx-z, SMH600PS03x-z, SMH600PS04x-z, SMH600PS05x-z											
	100-240ac	47-63	0	5.125dc	117.62	544.59	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS06-EFx-z, SMH600PS07-EFx-z, SMH600PS08-EFx-z, SMH600PS09-EFx-z, SMH600PS10-EFx-z, SMH600PS06-TFx-z, SMH600PS07-TFx-z, SMH600PS08-TFx-z, SMH600PS09-TFx-z, SMH600PS10-TFx-z, SMH600PS06x-z, SMH600PS07x-z, SMH600PS08x-z, SMH600PS09x-z, SMH600PS10x-z											
	100-240ac	47-63	0	10.035dc	66.12	632.96	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS11-EFx-z, SMH600PS12-EFx-z, SMH600PS13-EFx-z, SMH600PS11-TFx-z, SMH600PS12-TFx-z, SMH600PS13-TFx-z, SMH600PS11x-z, SMH600PS12x-z, SMH600PS13x-z [*r]											
	100-240ac	47-63	0	11 - 13dc	54.54	600	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS14-EFx-z, SMH600PS15-EFx-z, SMH600PS16-EFx-z, SMH600PS14-TFx-z, SMH600PS15-TFx-z, SMH600PS16-TFx-z, SMH600PS14x-z, SMH600PS15x-z, SMH600PS16x-z [*r]											
	100-240ac	47-63	0	13.5 - 16dc	44.44	600	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS17-EFx-z, SMH600PS18-EFx-z, SMH600PS19-EFx-z, SMH600PS20-EFx-z, SMH600PS21-EFx-z, SMH600PS17-TFx-z, SMH600PS18-TFx-z, SMH600PS19-TFx-z, SMH600PS20-TFx-z, SMH600PS21-TFx-z, SMH600PS17x-z, SMH600PS18x-z, SMH600PS19x-z, SMH600PS20x-z, SMH600PS21x-z [*r]											
	100-240ac	47-63	0	17 - 21dc	35.29	600	3	60950-1, 2nd Ed + AM1	20B	0	1

SMH600PS22-EFx-z, SMH600PS23-EFx-z, SMH600PS24-EFx-z, SMH600PS25-EFx-z, SMH600PS22-TFx-z, SMH600PS23-TFx-z, SMH600PS24-TFx-z, SMH600PS25-TFx-z, SMH600PS22x-z, SMH600PS23x-z, SMH600PS24x-z, SMH600PS25x-z											
	100-240ac	47-63	0	24.95dc	34.483	852.88	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS26-EFx-z, SMH600PS27-EFx-z, SMH600PS28-EFx-z, SMH600PS29-EFx-z, SMH600PS30-EFx-z, SMH600PS26-TFx-z, SMH600PS27-TFx-z, SMH600PS28-TFx-z, SMH600PS29-TFx-z, SMH600PS30-TFx-z, SMH600PS26x-z, SMH600PS27x-z, SMH600PS28x-z, SMH600PS29x-z, SMH600PS30x-z[*r]											
	100-240ac	47-63	0	26 - 30dc	23.07	600	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS31-EFx-z, SMH600PS32-EFx-z, SMH600PS33-EFx-z, SMH600PS34-EFx-z, SMH600PS35-EFx-z, SMH600PS36-EFx-z, SMH600PS37-EFx-z, SMH600PS38-EFx-z, SMH600PS39-EFx-z, SMH600PS40-EFx-z, SMH600PS31-TFx-z, SMH600PS32-TFx-z, SMH600PS33-TFx-z, SMH600PS34-TFx-z, SMH600PS35-TFx-z, SMH600PS36-TFx-z, SMH600PS37-TFx-z, SMH600PS38-TFx-z, SMH600PS39-TFx-z, SMH600PS40-TFx-z, SMH600PS31x-z, SMH600PS32x-z, SMH600PS33x-z, SMH600PS34x-z, SMH600PS35x-z, SMH600PS36x-z, SMH600PS37x-z, SMH600PS38x-z, SMH600PS39x-z, SMH600PS40x-z[*r]											
	100-240ac	47-63	0	31 - 40dc	19.35	600	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS41-EFx-z, SMH600PS42-EFx-z, SMH600PS43-EFx-z, SMH600PS44-EFx-z, SMH600PS45-EFx-z, SMH600PS46-EFx-z, SMH600PS47-EFx-z, SMH600PS48-EFx-z, SMH600PS49-EFx-z, SMH600PS50-EFx-z, SMH600PS41-TFx-z, SMH600PS42-TFx-z, SMH600PS43-TFx-z, SMH600PS44-TFx-z, SMH600PS45-TFx-z, SMH600PS46-TFx-z, SMH600PS47-TFx-z, SMH600PS48-TFx-z, SMH600PS49-TFx-z, SMH600PS50-TFx-z, SMH600PS41x-z, SMH600PS42x-z, SMH600PS43x-z, SMH600PS44x-z, SMH600PS45x-z, SMH600PS46x-z, SMH600PS47x-z, SMH600PS48x-z, SMH600PS49x-z, SMH600PS50x-z[*r]											
	100-240ac	47-63	0	41- 50dc	14.63	600	3	60950-1, 2nd Ed + AM1	20B	0	1
SMH600PS51-EFx-z, SMH600PS52-EFx-z, SMH600PS53-EFx-z, SMH600PS54-EFx-z, SMH600PS55-EFx-z, SMH600PS56-EFx-z, SMH600PS57-EFx-z, SMH600PS58-EFx-z, SMH600PS59-EFx-z, SMH600PS60-EFx-z, SMH600PS51-TFx-z, SMH600PS52-TFx-z, SMH600PS53-TFx-z, SMH600PS54-TFx-z, SMH600PS55-TFx-z, SMH600PS56-TFx-z, SMH600PS57-TFx-z, SMH600PS58-TFx-z, SMH600PS59-TFx-z, SMH600PS60-TFx-z, SMH600PS51x-z, SMH600PS52x-z, SMH600PS53x-z, SMH600PS54x-z, SMH600PS55x-z, SMH600PS56x-z, SMH600PS57x-z, SMH600PS58x-z, SMH600PS59x-z, SMH600PS60x-z											
	100-240ac	47-63	0	59.99dc	18.29	1090.66	3	60950-1, 2nd Ed + AM1	20B	0	1
SML150PS12, SML150PS13, SML150PS15[*r]											
	100-120/ 200-240ac	50-60	0	15	12.5	150	3	950	20B	0	0
SML150PS18[*r]											
	100-120/ 200-240ac	50-60	0	21	9.38	150	3	950	20B	0	0
SML150PS30, SML150PS48[*r]											
	100-120/ 200-240ac	50-60	0	41	4.84	150	3	950	20B	0	0
SML150PS48, SML150PS54[*r]											
	100-120/ 200-240ac	50-60	0	55	3.58	150	3	950	20B	0	0

XP0501x-18 (j)											
	100-240ac	47-63	0	21dc	14.37	230	3	60950-1	20B	2	1
				21dc	21.87	350	3				
XP0501x-24 (j)											
	100-240ac	47-63	0	30dc	10.45	230	3	60950-1	20B	2	1
				30dc	15.9	350	3				
XP0501x-36 (j)											
	100-240ac	47-63	0	41dc	7.41	230	3	60950-1	20B	2	1
				41dc	11.29	350	3				
XP0501x-48 (j)											
	100-240ac	47-63	0	53dc	5.47	230	3	60950-1	20B	2	1
				53dc	8.33	350	3				
XP0501x-54 (j)											
	100-240ac	47-63	0	60dc	4.25	230	3	60950-1	20B	2	1
				60dc	6.48	350	3				

[*r] - Output values are rated.

- Represents 0-9.

(#) - where X can be any number between 03 and 48

(&) - input range from -36 to -72 Vdc (+/- 0% tolerance)

(-P) - May be followed by suffix P.

(1) - [#] where Y= B or C

(2) - [+] where X= 05,12,15,24,30,48

(a) - Where Y = T, P, E, S or SD

(a1) - X can be any alphanumeric or blank

(AA) - Where XX can be any number between 3 and 48 designating the output voltage

(AB) - May also be provided with suffix "S" and/or "D", "-" provided optionally

(b) - z=blank, 0-9 , A-Z

(bb) - Rating B output max 155 W

(c1) - followed by C, CD, CL, or CDL

(c2) - followed by E, ED, EL, or EDL

(c3) - followed by F, FD, FL, or FDL

(c4) - Rating B output max 155 W

(cc) - Where xx can be alphanumeric or blank for marketing purposes only.

(d) - Denotes that other output voltages are available for the series; tested voltages noted only.

(gg) - 1st * = S, D, T or Q; 2nd to 3rd * = 00-48; 4th * = B, C, D or blank; 5th * = -C or blank

(h) - May be followed by suffix L

(i) - X may be - or blank; Y may be C, D, E, F or blank; Z may be B, D F or blank

(i1) - For input=100-130Vac

(i2) - For input=130-240Vac

(j) - x may blank or F

(k) - y may be Blank (without fan) or A (u-case + top cover)

(l) - y is Blank (without fan)

(m) - y is A (with fan)

(n) - y is C (for Enclosure)

(o) - y may be R, S or T

(p) - z may be A-Z, a-z, 0-9 or blank

(q) - output represents rated voltage

(r) - Values for max. V and max. A are output ratings

(s) - * may be blank, B or P; # may be blank or P

(t) - Y can be E, P, T or S; Z can be 0-9, A-Z or a-z

(u) - xxx will be 03 through 480 inclusively

(v) - 4.99 Volt output is for model CU20-10; 24 Volt output is for model CU20-14; 15.87 Volt output is for model CU20-16

(^) - where y can be blank, 0-9 or A -Z for marketing purposes.

* - Where X may be F or S; Y may be P or S; Z may be A or B

@ - Where Y can be E, P, T or S. [@] - Where x represents either blank or ?-?

w - where w can be H or blank.

X - X=05, 10 or 18

Y - Y=05, 12, 15 or 24

y = - z may be blank, 0-9 or A-Z for marketing use

Z - can be N or blank, zz = 0-9, A-Z or blank

[#] - X can be either P or U

[\$] - Where y represents either blank or C

[*r] - Output values are rated.

[++++] - Where xx can be alphanumeric or blank for marketing purposes only; yy can be 12, 15, 24, 30, 36, 48, 60 to represents output voltage.

[+] - YY may be any alphanumeric character or blank

[x] - X may be 10, 12, 13, 13-1, 14, 16, 17, 18, 23, 24, 25, 30, 31, 32, 33, 40, 41, 42, 44, 45; Z may be A-Z or Blank



Marking: Company name or trademark and model designation on the product or on the smallest unit container in which the product is packaged.

[Last Updated](#) on 2015-04-16

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2015 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".