

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

Product
Produit

Name and address of the applicant
Nom et adresse du demandeur

Name and address of the manufacturer
Nom et adresse du fabricant

Name and address of the factory
Nom et adresse de l'usine

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Trademark (if any)
Marque de fabrique (si elle existe)

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

Model / Type Ref.
Ref. De type

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{ème} page

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

CERTIFICAT D'ESSAI OC

Component Switching Power Supply

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

XP POWER INC
990 BENECIA AVE SUNNYVALE CA 94085-2804
UNITED STATES

☒ Additional Information on page 2

Input Rated: 100-240 Vac; 50/60 Hz; 2.2 A
Output Rated: Refer to Test Report for additional details.

XP



AHM180PSXXYY-ZZ
See Page 2

National Differences specified in the CB Test Report
☐ Additional Information on page 2

IEC 60601-1(ed.2), IEC 60601-1(ed.2);am1,
IEC 60601-1(ed.2);am2

E146893-A52-CB-1 issued on 2015-09-17

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- ☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-09-17

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-26003-UL

Model Details:

AHM180PSXXYY-ZZ (where XX is any number between 12-48 designating output voltage, where YY can be "C2" or blank, and -ZZ can be "-A", "-6", "-6A", "-8", "-8A", or blank)

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321
CHINA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIET NAM

Additional information (if necessary)

Information complémentaire (si nécessaire)



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-09-17

Signature:

Jolanta M. Wroblewska