

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Switching Brick Power Supply

Name and address of the applicant

XP POWER LTD
401 COMMONWEALTH DR HAW PAR TECHNOCENTRE
LOBBY B, #02-02 SINGAPORE 149598 SINGAPORE

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED
STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU
215321
CHINA Additional Information on page 2

Ratings and principal characteristics

Input Rated: 100-240 Vac, 50/60 Hz, 1.4 A
See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 1

Model / Type Ref.

ALM120PSXXYY-ZZ##V, See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 60950-1:2006/ A11:2009/ A1:2010/
A12:2011/ A2:2013. National Differences specified in the CB Test
Report. Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60950-1(ed.2), IEC 60950-1(ed.2);am1,
IEC 60950-1(ed.2);am2

As shown in the Test Report Ref. No. which forms part of this Certificate

E346017-A6-CB-1 issued on 2017-07-28

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2017-07-28

Signature:

Jan-Erik Storgaard

For full legal entity names see www.ul.com/ncbnames



Ref. Certif. No.

DK-65533-UL

Model Details:

ALM120PSXXYY-ZZ##V

(where XX is any number between 12-24 designating output voltage and YY can be blank or "C2" designating Class II configuration, and -ZZ can be blank or "-A", "-6", "-6A", "-8", "-8A" designating AC inlet type, and V can be any alphanumeric or blank designating casing colour)

Models may have an additional ## identifier which can be any alphanumeric or blank designating marketing purposes only.

Factories:

XP POWER INC
990 BENECIA AVE SUNNYVALE CA 94085
UNITED STATES

XP POWER (VIETNAM) CO LTD
LOT D - 4Q – CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

Ratings:

Output Rated:

- ALM120PS12: 12 Vdc (10.1 - 13.5 Vdc), 10 A max., 120W max.;
- ALM120PS15: 15 Vdc (13.5 - 17.0 Vdc), 8 A max., 120W max.;
- ALM120PS19: 19 Vdc (17.1 - 21.0 Vdc), 6.32 A max., 120W max.;
- ALM120PS24: 24 Vdc (21.0 - 26.0 Vdc), 5 A max., 120W max.

Additional information (if necessary)



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-07-28

Signature: 
Jan-Erik Storgaard