



Ref. Certif. No.

US-32854-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Brick Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER LLC
990 BENEZIA AVE
SUNNYVALE CA 94085
UNITED STATES

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

ALM85US15-XA1185, ALM85USXXYY-WZ##V
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6059-CB-1 issued on 2019-05-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-05-22

Original Issue Date: 2018-11-30

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-32854-M1-UL

Model Details:

ALM85USXXYY-WZ##V, where XX is any number between 12-24, YY can be blank or C2, W can be blank, 6, or 8, Z can be blank or A, # can be blank or any alphanumeric character, and V can be blank or any alphanumeric character, may be provided with or without "-".

Factories:

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
MY PHUOC 3 INDUSTRIAL PARK
BEN CAT DISTRICT
BINH DUONG BINH DUONG VIETNAM

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD
ZHANGPU TOWN
KUNSHAN
JIANGSU 215300 CHINA

Ratings:

INPUT: 100 - 240 V ~ 1.7A; 50/60Hz

OUTPUT:

Output voltage rating indicated in '()' under "Ratings" represents voltage tolerance evaluated.

ALM85US12: 12 Vdc (10.1 - 13.5 Vdc); 6.67 A max.; 80W max.;
ALM85US15: 15 Vdc (13.5 - 17.0 Vdc); 5.33 A max.; 80W max.;
ALM85US19: 19 Vdc (17.1 - 21.0 Vdc); 4.47 A max.; 85W max.;
ALM85US24: 24 Vdc (21.0 - 26.0 Vdc); 3.54 A max.; 85W max.;
ALM85US15-XA1185: 15 Vdc (13.5 - 17.0 Vdc); 5.33 A max.; 80W max.;

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

Summary of Modifications:

Updated Tables and Clauses.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/names

Date: 2019-05-22
Original Issue Date: 2018-11-30

Signature:

Jolanta M. Wroblewska