

US-32367-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Brick Power Supply

Name and address of the applicant

XP POWER L L C 15641 RED HILL AVE, SUITE 100

15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780

UNITED STATES

Name and address of the manufacturer

XP POWER L L C

15641 RED HILL AVE, SUITE 100

TUSTIN CA 92780 UNITED STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER (KUNSHAN) LTD

230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN

JIANGSU 215320

CHINA

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

AHM150PS12-XB0333, AHM150PSXXYY-ZW##V See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017. National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6011-CB-1 issued on 2018-08-30, E139109-A6011-CB-1 issued on 2018-08-28

This CB Test Certificate is issued by the National Certification Body



Date: 2018-08-31

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Signature:

For full legal entity names see www.ul.com/ncbnames

Jolanta M. Wroblewska



US-32367-UL

Model Details:

AHM150PSXXYY-ZW##V Where XX is any number between 12-48, YY can be blank or C2, Z can be blank or A, W can be blank, 6, or 8, # can be blank or any alphanumeric character, and V can be blank or any alphanumeric character, may be provided with or without "-".

Factories: XP POWER LLC 990 BENECIA AVE SUNNYVALE CA 94085 UNITED STATES

XP POWER (VIETNAM) CO LTD LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG BINH DUONG VIETNAM

Ratings: Input:

100 - 240V ac 1.8A, 50/60Hz

Output at 40°C (100% load):

Model AHM150PS12: 12 Vdc (10.1-13.5 Vdc), 12.5 A max. (150W max) Model AHM150PS15: 15 Vdc (13.6-17.0 Vdc), 10.0 A max. (150W max) Model AHM150PS19: 19 Vdc (17.1-21.0 Vdc), 7.89 A max. (150W max) Model AHM150PS24: 24 Vdc (21.1-26.0 Vdc), 6.25 A max. (150W max) Model AHM150PS28: 28 Vdc (26.1-31.0 Vdc), 5.36 A max. (150W max) Model AHM150PS33: 33 Vdc (31.1-33.0 Vdc), 4.55 A max. (150W max) Model AHM150PS36: 36 Vdc (33.1-42.0 Vdc), 4.17 A max. (150W max) Model AHM150PS48: 48 Vdc (42.1-54.0 Vdc), 3.13 A max. (150W max)

Output voltage rating indicated in parenthesis represents voltage tolerance evaluated.

All outputs are de-rated to 40% load at 60°C.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-08-31

Signature:

Jolanta M. Wroblewska