



Ref. Certif. No.

JPTUV-177541

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

SWITCHING POWER ADAPTOR

Name and address of the applicant

XP Power LLC
340 Commerce Suite 100 Irvine CA 92602
USA

Name and address of the manufacturer

XP Power LLC
340 Commerce Suite 100 Irvine CA 92602
USA

Name and address of the factory

Note: When more than one factory, please report on page 2

Xianglong Road, Huangzhou, New Town District, Shilong
Town, Dongguan, 523326 Guangdong, P.R. China

Ratings and principal characteristics

AC Input : 100-240V, 50/60Hz, 1.7A; Class II
DC Output: Refer to page 2

Trademark / Brand (if any)

XP

Customer's Testing Facility (CTF) Stage used

N/A

Model / Type Ref.

AMF60USXXXXXXXXXX
(XXX = 120-150 or 190-240, Y = 0-9, A-Z, '-' or blank)

Additional information (if necessary may also be reported on page 2)

See additional page(s) for further Additional information.
For model differences, refer to the test report.

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2018
See Test Report for National Differences

As shown in the Test Report Ref. No. which forms part of this Certificate

CN25AN0C 001

This CB Test Certificate is issued by the National Certification Body



TÜV Rheinland Japan Ltd.
4-25-2 Kita-Yamata, Tsuzuki-ku
Yokohama 224-0021, Japan
Mail: info@jpn.tuv.com

Date: 2025-09-17

Signature:

Handwritten signature and name: Martin Wang

10/061SMD 2024-12 rke-simplified

Additional information :

DC Output:

12.0V, 5.00A, 60.0W Max.
12.1-13.0V, 4.60A, 60.0W Max.
13.1-14.0V, 4.28A, 60.0W Max.
14.1-15.0V, 4.00A, 60.0W Max.
19.0V, 3.15A, 60.0W Max.
19.1-20.0V, 3.00A, 60.0W Max.
20.1-21.0V, 2.85A, 60.0W Max.
21.1-22.0V, 2.72A, 60.0W Max.
22.1-23.0V, 2.60A, 60.0W Max.
23.1-24.0V, 2.50A, 60.0W Max.