


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product	Switching Brick Power Supply
Name and address of the applicant	XP Power LLC 15641 Red Hill Ave., Ste. 100 Tustin, CA 92780 USA
Name and address of the manufacturer	XP Power Ltd. 401 Commonwealth Drive, Haw Par Technocentre, Lobby B, #02-02, Singapore 149598 Singapore
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP Power Inc. 990 Benecia Ave. Sunnyvale, CA 94085-2804 USA <input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	ALM120PSXXYY-ZZ##V See Page 2
Additional information (if necessary may also be reported on page 2)	National Differences specified in the CB Test Report. <input type="checkbox"/> <a href="#">Additional Information on page 2</a>
A sample of the product was tested and found to be in conformity with	IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1, IEC 60601-1-6(ed.3), IEC 60601-1-6(ed.3);am1
As shown in the Test Report Ref. No. which forms part of this Certificate	E146893-D1020-1/A0/C0-CB issued on 2018-04-19

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-04-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

**US-31634-UL**

**Model Details:**

ALM120PSXXYY-ZZ##V (where XX is any number between 12-24 designating output voltage and YY can be blank or "C2" designating Class II configuration, and -ZZ can be blank or "-A", "-6", "-6A", "-8", "-8A" designating AC inlet type, and V can be any alphanumeric or blank designating casing colour). Models may have an additional ## identifier which can be any alphanumeric or blank designating marketing purposes only. Model name can also include suffix identifier -SF to indicate a Single Fuse supplied for Class II configurations only.

**Factories:**

XP Power (Kunshan) Ltd  
230 Bin Jiang Nan Rd  
Zhangpu Town, Kunshan,  
Jiangsu 215321 China

XP Power (Vietnam) Co., Ltd.  
Lot D - 4Q-CN  
My Phuoc 3 Industrial Park  
Ben Cat District, Binh Duong Vietnam

XP Power  
Horseshoe Park  
Pangbourne RG8 7JW United Kingdom

**Ratings:**

Input: 100-240 Vac, 50/60 Hz, 1.4 A

**Output:**

ALM120PS12: 12 Vdc (10.1 - 13.5 Vdc), 10 A max., 120W max.;  
ALM120PS15: 15 Vdc (13.5 - 17.0 Vdc), 8 A max., 120W max.;  
ALM120PS19: 19 Vdc (17.1 - 21.0 Vdc), 6.32 A max., 120W max.;  
ALM120PS24: 24 Vdc (21.0 - 26.0 Vdc), 5 A max., 120W max

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2018-04-24

Signature:

Jolanta M. Wroblewska