



Ref. Certif. No.

DK-158291-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP Power Limited
19 Tai Seng Ave, #07-01, 534054,
Singapore

Name and address of the manufacturer

XP Power Limited
19 Tai Seng Ave, #07-01, 534054,
Singapore

Name and address of the factory

8-1 FU KUNG RD, FU HSING PARK, FU HSING HSIANG,
CHANGHUA HSIEN 506, TAIWAN

Note: When more than one factory, please report on page 2

☒ Additional Information on page 2

Ratings and principal characteristics

Input: 100-240 V~, 47-63 Hz, 5 A
Output: See test report for details.

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

CCR300PSYY-XXXXXXXXX

☒ Additional Information on page 2

Additional information (if necessary may also be reported on page 2)

National Differences: AU, CA, CN, EU Group Differences, JP, NZ, SA, GB, US

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2018

As shown in the Test Report Ref. No. which forms part of this Certificate

2408061-1-CB issued on 2024-09-10

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2024-10-08

Signature:

Thomas Wilson



Ref. Certif. No.

DK-158291-UL

Factory(ies):

No. 66 YUANYING RD, LIAOBU TOWN, DONGGUAN CITY GUANGDONG 523412,
P.R. China

Additional Model Detail(s):

CCR300PSYY-XXXXXXXXX,

“YY” can be 12, 15,24, 28, 30,48,54.

“XXXXXXXX” can be any alphanumeric or blank for market purpose only

Additionally evaluated to:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2024-10-08

Signature:

Thomas Wilson