


IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product	Switching Brick Power Supply
Name and address of the applicant	XP POWER LTD 401 COMMONWEALTH DR HAW PAR TECHNOCENTRE LOBBY B, #02-02 SINGAPORE 149598 SINGAPORE
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory <i>Note: When more than one factory, please report on page 2</i>	XP POWER (KUNSHAN) LTD 230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321 CHINA <input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 1
Model / Type Ref.	ALM150PSXXYY-ZZ##V See Page 2
Additional information (if necessary may also be reported on page 2)	Class I Additionally evaluated to EN 62368-1:2014 /A11:2017; National Difference specified in the CB Test Report <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1(ed.2)
As shown in the Test Report Ref. No. which forms part of this Certificate	E346017-A6004-CB-1 issued on 2018-04-26

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-04-27

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-72658-UL

Model Details:

ALM150PSXXYY-ZZ##V

(where XX is any number between 12-48 designating output voltage and YY can be blank, and -ZZ can be blank or "-A", "-6", "-6A", "-8", "-8A" designating AC inlet type, and V can be any alphanumeric or blank designating casing colour)

Models may have an additional ## identifier which can be any alphanumeric or blank designating marketing purpose only.

Factories:

XP POWER INC
990 BENECIA AVE SUNNYVALE CA 94085
UNITED STATES

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CNMY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

XP POWER PLC
HORESHOE PARK PANGBOURNE RG87 JW
UNITED KINGDOM

Ratings:

Input Rated:

100-240 Vac; 50/60 Hz; 1.8 A

Output Rated:

ALM150PS12: 12 Vdc (10.1 - 13.5 Vdc); 12.5 A max.; 150W max.;

ALM150PS15: 15 Vdc (13.5 - 17.0 Vdc); 10 A max.; 150W max.;

ALM150PS19: 19 Vdc (17.1 - 21.0 Vdc); 7.9 A max.; 150W max.;

ALM150PS24: 24 Vdc (21.0 - 26.0 Vdc); 6.2 A max.; 150W max.;

ALM150PS48: 48 Vdc (42.1 - 54.0 Vdc); 3.1 A max.; 150W max.

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-04-27

Signature:

Jan-Erik Storgaard