



Ref. Certif. No.

US-33356-M1-ULIEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**CB TEST CERTIFICATE**

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

*Note: When more than one factory, please report on page 2*XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU
215300
CHINA☒ Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECX40UYZZ, ECX60UYZZ
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6072-CB-1 issued on 2019-05-01

This CB Test Certificate is issued by the National Certification Body

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADAFor full legal entity names see www.ul.com/ncbnames

Date: 2019-05-03

Original Issue Date: 2019-03-11

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-33356-M1-UL

Model Details:

ECX40UYZZ, ECX60UYZZ

Where X is C or M, Y is D or T, ZZ is 21, 22, 31-37. May be followed by 3X5.

Factories:

XP POWER (VIETNAM) CO LTD

LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG BINH DUONG VIETNAM

XP POWER PLC

16 HORESHOE PARK PANGBOURNE RG8 7JW
UNITED KINGDOM

XP POWER LIMITED

LIPO BLDG, #05-01 621 ALJUNIED RD SINGAPORE 389834
SINGAPORE

XP POWER LLC

990 BENECIA AVE SUNNYVALE CA 94085
USA

Ratings:

ECX40UYZ:

INPUT~ 100-240VAC 50/60Hz1A

Total output max 40W.

Outputs (2 or 3 Provided) (Voltage ranges in parenthesis):

3.3 Vdc, 1.5A

3.3 Vdc, 6A

5 Vdc, 1.5A

5 Vdc, 6A

12 Vdc (10.1 to 13.5), 2A

-12 Vdc (-10.1 to -13.5), 0.5A

15 Vdc (13.6 to 17), 1.5A

-15 Vdc (-13.6 to -17), 0.5A

24 Vdc (21.1 to 26), 1A

ECX60UYZZ:

INPUT~ 100-240VAC 50/60Hz 1.5A

Total output max 60W.

Outputs (2 or 3 Provided) (Voltage ranges in parenthesis):

3.3 Vdc, 1.5A

3.3 Vdc, 8A

5 Vdc, 3A

5 Vdc, 8A

12 Vdc (10.1 to 13.5), 3A

-12 Vdc (-10.1 to -13.5), 0.5A

15 Vdc (13.6 to 17), 2.5A

-15 Vdc (-13.6 to -17), 0.5A

24 Vdc (21.1 to 26), 1.5A

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

- Conditions of Acceptability: Neutral fusing statement updated for clarity.
- Updated Clauses 5.4.3.3 and F.3.5.3 and Tables 4.1.2, B.2.6 and B.2.5

Additional information (if necessary)

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-05-03

Original Issue Date: 2019-03-11

Signature:

Jolanta M. Wroblewska