

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE

Product
Produit

Name and address of the applicant
Nom et adresse du demandeur

Name and address of the manufacturer
Nom et adresse du fabricant

Name and address of the factory
Nom et adresse de l'usine

Note: When more than one factory, please report on page 2
Note: Lorsque il y a plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

Trademark (if any)
Marque de fabrique (si elle existe)

Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais constructeur

Model / Type Ref.
Ref. De type

Additional information (if necessary may also be reported on page 2)
Les informations complémentaires (si nécessaire,, peuvent être indiqués sur la 2^{ème} page

A sample of the product was tested and found to be in conformity with
Un échantillon de ce produit a été essayé et a été considéré conforme à la

As shown in the Test Report Ref. No. which forms part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de référence qui constitue partie de ce Certificat

CERTIFICAT D'ESSAI OC

Component Switching Power Supply

XP POWER LLC
SUITE 150, 1241 E DYER ROAD
SANTA ANA, CA 92705, USA

XP POWER LLC
SUITE 150, 1241 E DYER ROAD
SANTA ANA, CA 92705, USA

XP POWER LLC.
990 BENEZIA AVE., SUNNYVALE CA 94085
USA

☒ Additional Information on page 2

See Page 2



SMT

ECS45US05, ECS25USXX, ECS45USXX
See Page 2

Additionally evaluated to EN 60601-1:2006/A1:2013; National Differences specified in the CB Test Report.

☐ Additional Information on page 2

IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

4786488107-20111006 issued on 2014-08-25

This CB Test Certificate is issued by the National Certification Body

Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA



UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN



UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2014-08-27

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-23830-UL

Model Details:

ECS25USXX, ECS45USXX (where XX can be any number between 12 and 48 designating the output voltage, may also be follow by suffix SF or -C or both)

Factories:

XP POWER (KUNSHAN) LTD.
230 BIN JIANG NAN RD., ZHANGPU TOWN, KUNSHAN, JIANGSU 215300
CHINA

Ratings:

Input Rating:

Model ECS45US05 and Model ECS45USXX Series: 100-240 Vac, 0.9 A, 50/60 Hz

Model ECS25USXX Series: 100-240 Vac, 0.6 A, 50/60 Hz

Output Rating:

All Series: See Model Differences in Test Report for details.

Additional information (if necessary)

Information complémentaire (si nécessaire)



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2014-08-27

Signature:

Jolanta M. Wroblewska