



Ref. Certif. No.

**US-30864-M2-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME

## CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780 USA

Name and address of the factory

*Note: When more than one factory, please report on page 2*

XP POWER INC  
990 BENECIA AVE SUNNYVALE CA 94085  
USA

☒ [Additional Information on page 2](#)

Ratings and principal characteristics

Model ECS65USXX Series:  
Input: 100-240VAC, 1.2A, 50/60 Hz  
See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECS65US12, ECS65USXX  
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.

☒ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6003-CB-1 issued on 2020-01-09

This CB Test Certificate is issued by the National Certification Body



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2020-01-09

Original Issue Date: 2017-11-22

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

**US-30864-M2-UL**

**Model Details:**

ECS65USXX

(where XX can be any number between 12 and 48 designating the output voltage), may also be provided with suffix "SF" and/or "-B"

**Factories:**

XP POWER (KUNSHAN) LTD  
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321  
CHINA

XP POWER (VIETNAM) CO LTD  
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG  
VIETNAM

XP POWER PLC  
HORESHOE PARK PANGBOURNE RG87 JW  
UNITED KINGDOM

**Ratings:**

Model ECS65US12:

Input: 100-240VAC, 1.2A, 50/60 Hz or 100-240VAC, 1.2A, 50/60/400 Hz

Output: See Enclosure - Miscellaneous: Ratings Table for details.

**Additional Information:**

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

**Amendment 2 (Technical):**

- Updated report from Pollution Degree 2 to Pollution Degree 3.
- Revised Test Item Particulars, General Product Information 1 - Conditions of Acceptability - Pollution Degree.
- Updated General Product Information 2.
- Revised sub-clauses 5.4.1.5 and 5.4.3.1 to indicate PD3.
- Revised minimum required creepage distances per PD3 in Table 5.4.2.2.

**Additional information (if necessary)**



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

**Date:** 2020-01-09

Original Issue Date: 2017-11-22

**Signature:**

Jolanta M. Wroblewska