



Ref. Certif. No.

DK-180162-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	XP Power Limited 19 Tai Seng Avenue #7-01 Singapore 534054
Name and address of the manufacturer	XP Power Limited 19 Tai Seng Avenue #7-01 Singapore 534054
Name and address of the factory	8-1 FU KUNG RD, FU HSING PARK, FU HSING HSIANG, CHANGHUA HSIEN 506, TAIWAN ☒ Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Input: 100-240 V~, 10 A, 47-63 Hz 134-334 V DC, 10 A Output: See test report for details.
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	CCR750PSYY-XXXXXXXX ☒ Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	Evaluated to National or Group Differences for AR, AU, CA, CN, EU Group Differences, JP, NZ, KR, SA, GB, US ☒ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2604017-2-CB issued on 2026-05-04

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-05-08

Signature:


Thomas Wilson



Ref. Certif. No.

DK-180162-UL

Factory(ies):

No. 66 YUANYING RD, LIAOBU TOWN, DONGGUAN CITY GUANGDONG 523412,
P. R. CHINA

Additional Model Detail(s):

CCR750PSYY-XXXXXXXXX,

“YY” can be 12, 15, 24, 28, 30, 36, 48, 54.

“XXXXXXXX” can be any alphanumeric or blank for market purpose only.

“-” optionally provide.

Evaluated to National Differences declared for:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-05-08

Signature:

Thomas Wilson