

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE**CERTIFICAT D'ESSAI OC**

Product
Produit

Component Switching Power Supply

Name and address of the applicant
Nom et adresse du demandeur

XP Power LLC
Suite 100, 15641 Red Hill Ave, Tustin, CA 92780 USA

Name and address of the manufacturer
Nom et adresse du fabricant

XP Power LLC
Suite 100, 15641 Red Hill Ave, Tustin, CA 92780 USA

Name and address of the factory
Nom et adresse de l'usine

XP Power LLC,
990 Benecia Ave, Sunnyvale CA 94085,
USA

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

[Additional Information on page 2](#)

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

See Page 2

Trademark (if any)
Marque de fabrique (si elle existe)



Type of Manufacturer's Testing Laboratories used
Type de programme du laboratoire d'essais
constructeur

Model / Type Ref.
Ref. De type

GCS150PSxxKyy, GCS150PSxxyy, GCS180PSxxyy
See Page 2

Additional information (if necessary may also be
reported on page 2)
Les informations complémentaires (si nécessaire,,
peuvent être indiqués sur la 2^{ème} page

Additionally evaluated to EN 60601-1:2006 / A1:2013 /
A12:2014; National Differences specified in the CB Test Report.

[Additional Information on page 2](#)

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

IEC 60601-1(ed.3), IEC 60601-1(ed.3);am1

As shown in the Test Report Ref. No. which forms
part of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue partie de ce Certificat

4786488107-20140916 issued on 2015-04-02

This CB Test Certificate is issued by the National Certification Body

Ce Certificat d'essai OC est établi par l'Organisme **National de Certification**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-04-27

Signature:

Original Issue Date: 2014-10-09

Jolanta M. Wroblewska



Ref. Certif. No.

US-24048-A1-UL

Model Details:

GCS150PSxxKyy,GCS150PSxxyy (where xx can be any number between 12 and 48 and yy is "-C", "-TF", "-EF" or blank and may be preceded by "-R"; all "-" considered optional; may also be provided with additional suffix "SF" or "S")

GCS180PSxxyy (where xx can be any number between 12 and 48 and yy is "-C", "-TF", "-EF", or blank and may be preceded by "-R"; all "-" considered optional; may also be provided with additional suffix "SF" or "S")

Factories:

XP Power (Kunshan) Limited.,
230, Bin Jiang Nan Road, Zhang Pu Town, Kunshan, Jiangsu 215300
China

Ratings:

GCS150PSxxyy and GCS150PSxxKyy series

Input: 100-240 Vac, 50/60 Hz, 1.8A

Output: See Test Report - Model Differences for details

GCS180PSxxyy series

Input: 100-240 Vac, 50/60 Hz, 2.2A

Output: See Test Report - Model Differences for details

Additional Information:

The original report was modified to include the following changes/additions:

Modify model description, applicant/manufacturer address, critical components table and enclosures information, see test report.

Additional information (if necessary)

Information complémentaire (si nécessaire)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA



UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK



UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN



UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2015-04-27

Original Issue Date: 2014-10-09

Signature:

Jolanta M. Wroblewska