

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME**
**CB TEST CERTIFICATE**

Product

Power Supply

Name and address of the applicant

XP POWER LTD  
401 Commonwealth Drive, Haw Par Technocentre, Lobby B,  
#02-02, Singapore 149598

Name and address of the manufacturer

XP POWER LTD  
401 Commonwealth Drive, Haw Par Technocentre, Lobby B,  
#02-02, Singapore 149598

Name and address of the factory

No. 33, Sec. 2, Renhe Rd., Daxi Township, Taoyuan County  
33548  
Taiwan

*Note: When more than one factory, please report on page 2*
☒ [Additional Information on page 2](#)

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)

XP Power



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

HDL3000PSxxxxxxxxx  
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017  
National Difference specified in the CB Test Report

☐ [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

1910029-CB issued on 2019-10-28

This CB Test Certificate is issued by the National Certification Body



- ☐ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2019-11-25

Signature:



Jan-Erik Storgaard

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

**Model Details:**

HDL3000PSxxxxxyyyyyy

"xxx" = 150, 200, 250, 300, 400 to denote output voltage  
and "y" may be any alphanumeric character, "-" or blank

**Factories:**

Building 121, Arising Sun Industrial City, No.13, Xinan Road, Lin Village, Tangxia Town, Dongguan City, Guangdong Province,  
China

**Ratings:**
**Input:**

115-180Vac, 47/63Hz, 19.7A (Max. Output Power 2000W)

200-240Vac, 47/63Hz, 14.5A (Max. Output Power 3000W)

**Output:**

150Vdc / 20A (for Model HDL3000PS150yyyyyy)

200Vdc / 15A (for Model HDL3000PS200yyyyyy)

250Vdc / 12A (for Model HDL3000PS250yyyyyy)

300Vdc / 10A (for Model HDL3000PS300yyyyyy)

400Vdc / 7.5A (for Model HDL3000PS400yyyyyy)

**Additional information (if necessary)**


UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-11-25

Signature:



Jan-Erik Storgaard