



Ref. Certif. No.

US-30862-M1-ULIEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**CB TEST CERTIFICATE**

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

*Note: When more than one factory, please report on page 2*ABES TECHNOLOGY CO LTD
NO 78-1 ZHANGMA ST XIUSHUI SHIANG CHANGHUA
COUNTY 504
TAIWAN☒ Additional Information on page 2

Ratings and principal characteristics

Input: 100-240 Vac, 2.5 A, 50/60 Hz
See Page 2

Trademark (if any)

XP



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 2

Model / Type Ref.

ECP150PS12-XE0358B, ECP150PS15-XA1014A,
ECP150PSXX
See Page 2Additional information (if necessary may also be
reported on page 2)

The report was revised to include technical modifications.

☒ Additional Information on page 2A sample of the product was tested and found
to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part
of this Certificate

E317867-A6005-CB-1 issued on 2019-07-17

This CB Test Certificate is issued by the National Certification Body



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-07-22

Signature:

Original Issue Date: 2017-11-21

Jolanta M. Wroblewska



Ref. Certif. No.

US-30862-M1-UL

Model Details:

ECP150PSXX (where XX can be any number between 12 and 48 designating the output voltage), may also be provided with suffix "SF".

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215321
CHINA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIETNAM

Ratings:

Output:

Model ECP150PS12: Output Rated: 12 Vdc, 12.5 A
Model ECP150PS15: Output Rated: 15 Vdc, 10 A
Model ECP150PS24: Output Rated: 24 Vdc, 6.25 A
Model ECP150PS28: Output Rated: 28 Vdc, 5.4 A
Model ECP150PS48: Output Rated: 48 Vdc, 3.1 A
Model ECP150PS12-XE0358B: Output Rated: 12 Vdc, 12.5 A
Model ECP150PS15-XA1014A: Output Rated: 15 Vdc, 10 A

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

- CBTL updated from "Camas WA" to "Vancouver WA".
- IT Power Systems evaluation added.
- Updated Conditions of Acceptability, Clause 5.5.2.2, Table 5.5.2.2
- Additional Information: Further information added about tests waived and performed.
- Added A11:2017 to EN 62368 in additional standards.
- Clause F.3.5.3: Comment updated for clarity.
- Updated Tables 4.1.2, 5.2, 5.4.9, B.2.5

Additional information (if necessary)



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

☐ UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nccnames

Date: 2019-07-22

Original Issue Date: 2017-11-21

Signature:

Jolanta M. Wroblewska