



Ref. Certif. No.

US-36561-UL

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**

CB TEST CERTIFICATE

Product

Component, power supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN, CA 92780 USA

Name and address of the factory

XP Power
Horseshoe Park
Pangbourne, RG8 7JW United Kingdom

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

HPA1K5PSXX Series
See Page 2

Additional information (if necessary may also be reported on page 2)

National Differences specified in the CB Test Report.
 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1044-1/A0/C0-CB issued on 2020-08-31

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-09-09

Signature:

Jolanta M. Wroblewska



Model Details:

HPA1K5PSXX Series where XX can be 24 or 48 which represents rated output voltage. The model may or may not be followed by -SF, where SF representing single fuse.

Factories:

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD
ZHANGPU TOWN
KUNSHAN, 215300 JIANGSU China

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
My Phuoc 3 Industrial Park
Ben Cat District
Binh Duong, Binh Duong Viet Nam

XP Power LLC
990 Benecia Ave
Sunnyvale, CA 94085 USA

Ratings:

HPA1K5PS24 – Input: 100-180V~, 16A, 50/60Hz or 180-240V~, 10A, 50/60Hz

HPA1K5PS48 – Input: 100-180V~, 16A, 50/60Hz or 180-240V~, 10A, 50/60Hz

Output: See models differences in Test Report for output details.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-09-09

Signature:

Jolanta M. Wroblewska