

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME

CB TEST CERTIFICATE

Product

Build in power supply

Name and address of the applicant

XP Power LLC
15641 Red Hill Ave, Suite 100
Tustin, CA 92780 USA

Name and address of the manufacturer

XP Power LLC
15641 Red Hill Ave, Suite 100
Tustin, CA 92780 USA

Name and address of the factory

Note: When more than one factory, please report on page 2

XP Power LLC
990 Benecia Ave Sunnyvale, CA 94085
USA Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

ECS100US12-B-XE0399, ECS100USxx-By
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1038-1/A2/C0-ULCB issued on 2019-10-18

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-10-31

Original Issue Date: 2019-06-13

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-33828-M1-UL

Model Details:

ECS100USxx-By (where xx can be any number between 12 and 48 designating the output voltage, y can be blank or SF). Models with suffix SF designate single fuse.

Factories:

XP Power (Kunshan) Limited
230 Bin Jiang Nan RoadZhang Pu Town, Kunshan Jiangsu 215300
China

Ratings:

Models ECS100USxx-By:

Input Rated: 100-240 V~, 1.9A, 50/60 Hz

Output Rated: See Enclosure - Miscellaneous 7-01 for maximum output details.

Model ECS100US12-B-XE0399:

Input Rated: 100-240 V~, 1.9A, 50-60 Hz

Output Rated: 12Vdc, 8.34A

Additional Information:

National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:
Added alternate bleeding resistors (R26, R27) to the critical component list.
See Test Report.

Additional information (if necessary)



-
-
-
-

UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-10-31

Original Issue Date: 2019-06-13

Signature:

Jolanta M. Wroblewska