



Ref. Certif. No.

US-33661-M1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

FU HSING PARK FU HSING HSIANG CHANGHUA
HSIEN 506
TAIWAN

Note: When more than one factory, please report on page 2

[Additional Information on page 2](#)

Ratings and principal characteristics

Ratings are for reference only.
See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

JCA04XXYZZ, JCA0605D01#30041-01, JCA06XXYZZ
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.
 [Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E317867-A6040-CB-1 issued on 2020-07-24

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2020-07-27
Original Issue Date: 2019-05-10

Signature:

Jolanta M. Wroblewska

For full legal entity names see www.ul.com/ncbnames



Ref. Certif. No.

US-33661-M1-UL

Model Details:

JCA04XXYZZ, JCA06XXYZZ
(where XX is 05, 12, 24, or 48, Y is S or D, ZZ is 01-15)

Factories:

DONGCHENG FOREIGN TRADE INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT
DONGGUAN GUANGDONG 523128
CHINA

Ratings:

Ratings are for reference only.

Input:

JCA04XXYZZ Series
4.5 - 9.0 VDC (5 Vdc, 1000mA)
9 - 18 VDC (12 Vdc, 440mA)
18 - 36 VDC (24 Vdc, 220mA)
36 - 75 VDC (48 Vdc, 110mA)

JCA06XXYZZ Series

4.5 - 9.0 VDC (5 Vdc, 1450mA)
9 - 18 VDC (12 Vdc, 600mA)
18 - 36 VDC (24 Vdc, 300mA)
36 - 75 VDC (48 Vdc, 150mA)

JCA0605D01#30041-01:

6.25 - 16.0 VDC (1450mA)

Output:

See Model Differences for details.

Additional Information:

Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

Amendment 1 (Technical):

Repeated Tests conducted in Tables B.3 and B.4 and recorded complete test results including maximum measured temperatures on T1.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2020-07-27

Original Issue Date: 2019-05-10

Signature:

Jolanta M. Wroblewska