

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME****CB TEST CERTIFICATE**

## Product

Component power supply for building-in and supplying regulated power to medical equipment.

## Name and address of the applicant

XP POWER LLC  
15641 RED HILL AVE., STE 100  
TUSTIN, CA 92780 USA

## Name and address of the manufacturer

XP POWER LLC  
15641 RED HILL AVE., STE 100  
TUSTIN, CA 92780 USA

## Name and address of the factory

*Note: When more than one factory, please report on page 2*XP POWER INC  
990 BENECIA AVE SUNNYVALE, CA 94085  
USA [Additional Information on page 2](#)

## Ratings and principal characteristics

Input: GCS350PS: 100-240Vac, 50/60, 4.9A,  
AVPQ150M165170Z: 100-240VAC 50/60Hz 1.9A.  
Output: See Model Differences in Test Report for details.

## Trademark (if any)



## Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

## Model / Type Ref.

AVPQ150M165170Z, GCS350PSxxyy  
See Page 2

## Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications.

 [Additional Information on page 2](#)

## A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005

## As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1003-3/A2/C0-CB issued on 2019-02-12

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-02-13

Original Issue Date: 2016-11-03

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

**US-28804-A2-UL**

**Model Details:**

GCS350PSxxyy where xx can be any number between 12 and 56 and yy is -C, -TF, -EF or blank; all - considered optional; may also be provided with additional suffix SF, S, J and AVPQ150M165170Z

**Factories:**

XP POWER (KUNSHAN) LTD  
230 BIN JIANG NAN RD., ZHANGPU TOWN KUNSHAN ,JIANGSU 215321  
CHINA

XP POWER (VIETNAM) CO., LTD.  
LOT D-4Q-CN, MY PHOUC 3 INDUSTRIAL PARK BEN CAT DISTRICT, BINH DUONG  
VIETNAM

XP POWER  
HORSESHOE PARK PANGBOURNE RG8 7JW  
UNITED KINGDOM

**Additional Information:**

Additionally evaluated to EN 60601-1:2006/A1:2013/A12:2014; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:  
To cover the addition of Resistors R86, R87, R88, and R89, 61.9kOhms each.  
Updates were made to clauses, where Humidity was updated to 48H.  
See Test Report.

**Additional information (if necessary)**



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-02-13  
Original Issue Date: 2016-11-03

Signature:

Jolanta M. Wroblewska