



Ref. Certif. No.

DK-181391-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	DC-DC Converter
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory	No.66 Yuanying Rd., Liaobu Town, Dongguan City, Guangdong 523412, China ☒ Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	(Optional) Input: 9-36 Vdc, 8.0 A ☒ Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	QAM60T24OXX, QAM60T24OXX-N ☒ Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	The risk management requirements of the standard were not addressed Evaluated to National or Group Differences for CA, JP, CH, US ☐ Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012, IEC 60601-1:2005/AMD2:2020
As shown in the Test Report Ref. No. which forms part of this Certificate	2601012-CB issued on 2026-06-01

This CB Test Certificate is issued by the National Certification Body



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-05

Signature


Thomas Wilson



Ref. Certif. No.

DK-181391-UL

Factory(ies):

No. 8-1 Fu Kung Rd., Fu Hsing Park Fu Hsing Hsiang, Chang Hua Hsien, 506
Taiwan

Additional Model Detail(s):

QAM60T24OXX, QAM60T24OXX-N, (Where O=S or D, XX=05,12,15 or 24)

Additional Ratings:

Output:

- (1) 5 Vdc, 12 A, 60 W (for Model QAM60T24S05, QAM60T24S05-N)
- (2) 12 Vdc, 5.0 A, 60 W (for Model QAM60T24S12, QAM60T24S12-N)
- (3) 15 Vdc, 4.0 A, 60 W (for Model QAM60T24S15, QAM60T24S15-N)
- (4) 24 Vdc, 2.5 A, 60 W (for Model QAM60T24S24, QAM60T24S24-N)
- (5) ± 12 Vdc, ± 2.5 A, 60 W (for Model QAM60T24D12, QAM60T24D12-N)
- (6) ± 15 Vdc, ± 2.0 A, 60 W (for Model QAM60T24D15, QAM60T24D15-N)

Additional information (if necessary)



- ☐ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☒ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2026-06-05

Signature:

Thomas Wilson