



Ref. Certif. No.

**US-33117-M2-UL**

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

**CB TEST CERTIFICATE**

Product

Power Rack

Name and address of the applicant

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the manufacturer

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the factory

Note: When more than one factory, please report on page 2

XP POWER LLC  
990 BENECIA AVE SUNNYVALE CA 94085  
UNITED STATES

[Additional Information on page 2](#)

Ratings and principal characteristics

INPUT: 100-240VAC 50/60Hz, 10A MAX PER SLOT  
Output Ratings: See Model Differences section for details.

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

GFR1K5RACK-0X  
See Page 2

Additional information (if necessary may also be reported on page 2)

The report was revised to include technical modifications

[Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6070-CB-1 issued on 2019-11-21

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-11-27

Original Issue Date: 2019-01-24

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

**US-33117-M2-UL**

**Model Details:**

GFR1K5RACK-0X (Where X is between 1-9.)

**Factories:**

XP POWER (VIETNAM) CO LTD  
LOT D - 4Q - CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG BINH DUONG  
VIETNAM

XP POWER (KUNSHAN) LTD  
230 BIN JIANG NAN RD ZHANGPU TOWN KUNSHAN JIANGSU 215300  
CHINA

**Additional Information:**

Additionally evaluated to EN 62368-1:2014/A11:2017; National Differences specified in the CB Test Report.

The original report was modified to include the following changes/additions:

- Ratings: Split input ratings for UL and CB and added max rated input current per slot.
- Updated marking plate with split input ratings for UL and CB and max rated input current per slot.
- Clause F.3.5.3: Comment added.
- Table 4.1.2: Corrected component power supply input current rating.
- Table B.2.5: Reformatted for clarity and input currents corrected.
- Japan National Differences evaluated.
- Clause 1.1 (US/CAN ND): Comment added.
- Enclosures: CB Test Certificate for component power supplies updated.

**Additional information (if necessary)**



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/names](http://www.ul.com/names)

**Date:** 2019-11-27  
**Original Issue Date:** 2019-01-24

**Signature:**

Jolanta M. Wroblewska