



Ref. Certif. No.

**DK-157721-UL**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product	Power Supply
Name and address of the applicant	XP Power LLC 340 Commerce, Suite 100, Irvine, CA 92602, United States
Name and address of the manufacturer	XP Power LLC 340 Commerce, Suite 100, Irvine, CA 92602, United States
Name and address of the factory	No 33 Sec 2 Renhe Rd Daxi District Taoyuan City, 33548 Taiwan
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	100-240VAC, 50/60Hz, 18-9A
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	HDA1500PSXXX-YYY-ZZZZZZ <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	National Differences: AR, AU, CA, CN, EU Group Differences, JP, NZ, KR, SA, GB, US <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2024-0319-01-1-A0-C0 issued on 2024-09-11

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2024-09-18

Signature:  
Thomas Wilson



Ref. Certif. No.

**DK-157721-UL**

**Factory(ies):**

Building 121, Arising Sun Industrial City, No.13, Xinan Road, Lin Village, Tangxia Town, Dongguan City, Guangdong Province, China

**Additional Model Detail(s):**

HDA1500PSXXX-YYY-ZZZZZZ, (Where XXX=400, 250, 150, 120 for output voltage, Y and Z = 0-9, A-Z or blank for marketing purposes only)

**Additionally evaluated to:**

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

**Additional information (if necessary)**



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2024-09-18

Signature:



Thomas Wilson

