



Ref. Certif. No.

US-36561-A1-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Component, power supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780
United States

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780
United States

Name and address of the factory

XP Power
Horseshoe Park Pangbourne RG8 7JW
United Kingdom

Note: When more than one factory, please report on page 2

[Additional Information on page 2](#)

Ratings and principal characteristics

HPA1K5PS24 – Input: 100-180V~, 16A, 50/60Hz or
180-240V~, 10A, 50/60Hz

[Additional Information on page 2](#)

Trademark / Brand (if any)



Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

HPA1K5PSXX may or may not followed by -SF

[Additional Information on page 2](#)

Additional information (if necessary may also be reported on page 2)

National Differences specified in the CB Test Report.
The report was revised to include administrative modifications.

[Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 60601-1:2005, IEC 60601-1:2005/AMD1:2012

As shown in the Test Report Ref. No. which forms part of this Certificate

E146893-D1044-1/A2/C0-CB issued on 2023-03-03

This CB Test Certificate is issued by the National Certification Body



- ☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-03-15

Original Issue Date: 2020-09-09

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36561-A1-UL

Factory(ies):

XP Power LLC
990 Benecia Ave Sunnyvale, CA 94085
United States

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD
ZHANGPU TOWN KUNSHAN, JIANGSU, 215300
China

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
My Phuoc 3 Industrial Park
Ben Cat District Binh Duong
Vietnam

Additional Model Detail(s):

HPA1K5PSXX may or may not followed by -SF, HPA1K5PSXX Series, where XX can be 24, 36, 48 or 60 which represents rated output voltage. The model may or may not followed by -SF, where SF representing single fuse.

Additional Ratings:

HPA1K5PS36 – Input: 100-180V~, 16A, 50/60Hz or
180-240V~, 10A, 50/60Hz

HPA1K5PS48 – Input: 100-180V~, 16A, 50/60Hz or
180-240V~, 10A, 50/60Hz

HPA1K5PS60 – Input: 100-180V~, 16A, 50/60Hz or
180-240V~, 10A, 50/60Hz

Output: See Test Report models differences for output details

Summary of Modifications:

Corrections to clauses, test tables, Engineering Conditions of Acceptability, and modification date. See CB Test Report for details.

Additional information (if necessary)



- ☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2023-03-15

Signature:

Original Issue Date: 2020-09-09

Jolanta M. Wroblewska