

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER LTD
401 COMMONWEALTH DR HAW PAR TECHNOCENTRE
LOBBY B, #02-02 SINGAPORE 149598
SINGAPORE

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE SUITE 100 TUSTIN CA 92780
USA

Name and address of the factory

Note: When more than one factory, please report on page 2

1 JING XIANG RD DONGCHENG FOREIGN TRADE
INDUSTRIAL PARK ZHUSHAN DONGCHENG
DISTRICT DONGGUAN 523128 GUANGDONG
CHINA Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

VCE03USXX
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014.

 Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1(ed.2)

As shown in the Test Report Ref. No. which forms part of this Certificate

E346017-A6001-CB-1 issued on 2017-12-29

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-12-29

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-69523-UL

Model Details:

VCE03USXX (where XX can be any number between 03 and 48 designating the output voltage), may also be provided with suffix "-P" optionally for open frame type.

Factories:

8-1 FU KUNG RD FU HSING PARK FU HSING HSIANG CHANGHUA HSIEN 506
TAIWAN

Ratings:

Input Rated: 100-277 Vac, 0.1 A, 50/60 Hz.

Output Rated:

- VCE03US03: 3.3 Vdc (2.95 - 3.65 Vdc), 0.910 A max., 3W max.;
- VCE03US05: 5 Vdc (4.5 - 5.5 Vdc), 0.600 A max., 3W max.;
- VCE03US09: 9 Vdc (8.1 - 10 Vdc), 0.333 A max., 3W max.;
- VCE03US12: 12 Vdc (10.1 - 13.5 Vdc), 0.250 A max., 3W max.;
- VCE03US15: 15 Vdc (13.5 - 17 Vdc), 0.200 A max., 3W max.;
- VCE03US24: 24 Vdc (21.1 - 26 Vdc), 0.125 A max., 3W max.;
- VCE03US48: 48 Vdc (42.1 - 52 Vdc), 0.063 A max., 3W max.;

Additional information (if necessary)



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2017-12-29

Signature:

Jan-Erik Storgaard