

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)  
CB SCHEME**

**CB TEST CERTIFICATE**

Product

Switching Power Supply

Name and address of the applicant

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the manufacturer

XP POWER L L C  
15641 RED HILL AVE, SUITE 100  
TUSTIN CA 92780  
UNITED STATES

Name and address of the factory

*Note: When more than one factory, please report on page 2*

CHANNEL WELL TECHNOLOGY (GUANGZHOU) CO LTD  
BLDG B  
EASTERN HI-TECH INDUSTRIAL BASE ZENGJIANG STR,  
ZENGCHENG GUANGZHOU GUANGDONG 511300  
CHINA

☐ Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

VCT40USX, VCT60USY  
See Page 2

Additional information (if necessary may also be reported on page 2)

☒ Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E317867-A6035-CB-1 issued on 2019-01-14

This CB Test Certificate is issued by the National Certification Body



☒ UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA  
☐ UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK  
☐ UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN  
☐ UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2019-01-16

Signature:

Jolanta M. Wroblewska

**Model Details:**

VCT40USX,VCT60USY Where X is 05, 053, Y is 12, 15, 16, 18, 19, 20, 24, 30.

**Ratings:**

Model VCT40US05

INPUT ~ 100-240VAC, 1.0A 50-60Hz, 400Hz

OUTPUT: 5V dc 8A 40W max

Model VCT40US053

INPUT ~ 100-240VAC, 1.0A 50-60Hz, 400Hz

OUTPUT: 5.3V dc 7.55A 40W max

Model VCT60US12

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 12V dc 5.00A

Model VCT60US15

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 15V dc 4.00A

Model VCT60US16

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 16V dc 3.75A

Model VCT60US18

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 18V dc 3.33A

Model VCT60US19

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 19V dc 3.16A

Model VCT60US20

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 20V dc 3.00A

Model VCT60US24

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 24V dc 2.50A

Model VCT60US30

INPUT ~ 100-240VAC, 1.7A 50-60Hz, 400Hz

OUTPUT: 30V dc 2.00A

**Additional Information:**

Additionally evaluated to EN 62368-1:2014 /A11:2017

National Difference specified in the CB Test Report

**Additional information (if necessary)**


UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/nbnames](http://www.ul.com/nbnames)

Date: 2019-01-16

Signature:

Jolanta M. Wroblewska

