



Ref. Certif. No.

US-36205-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

AC-DC Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100
TUSTIN CA 92780
UNITED STATES

Name and address of the factory

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD
ZHANGPU TOWN
KUNSHAN
JIANGSU 215300 CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

See Page 2

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

HPL5K0TSxxx Series,
where x can be 0 to 9 which represents rated output voltage.

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014 / A11:2017;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-A6091-CB-1 issued on 2020-07-20

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-22

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-36205-UL

Factories:

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
MY PHUOC 3 INDUSTRIAL PARK
BEN CAT DISTRICT
BINH DUONG BINH DUONG VIETNAM

XP POWER PLC
16 HORESHOE PARK
PANGBOURNE
RG8 7JW UNITED KINGDOM

XP POWER LIMITED
LIPO BLDG, #05-01
621 ALJUNIED RD
SINGAPORE 389834 SINGAPORE

XP POWER LLC
990 BENECIA AVE
SUNNYVALE CA 94085
UNITED STATES

Ratings:

Input:

3 Phase (3W+PE), 50/60Hz
200-240V, 19A MAX/PHASE

Output:

HPL5K0TS060: 0-60Vdc (0-63Vdc)/83.3A MAX, 5000W MAX.
HPL5K0TS100: 0-100Vdc (0-105Vdc)/50A MAX, 5000W MAX.
HPL5K0TS200: 0-200Vdc (0-210Vdc)/25A MAX, 5000W MAX.
All Models are provided with an isolated 5Vsb/2A output.

Additional information (if necessary)



- UL (US), 333 Pfinqsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-22

Signature:

Jolanta M. Wroblewska