



Ref. Certif. No.

US-45012-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	AC-DC Power Supply
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory	XP POWER PLC 16 Horeshoe Park Pangbourne RG8 7JW United Kingdom Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	HPT5K0TS400: 3-Phase (3W+PE), 50/60 Hz Input 200-240V, 11A MAX/PHASE Input 380-480V, 10A MAX/PHASE Additional Information on page 2
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	HPT5K0TS400, HPT5K0TS800
Additional information (if necessary may also be reported on page 2)	National Differences: AU, CA, CN, DK, EU Group Differences, FI, JP, NZ, NO, KR, SG, SE, GB, US Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	E139109-A6123-CB-1 issued on 2025-03-26

This CB Test Certificate is issued by the National Certification Body



☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
☐ UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-03-26

Signature:

Mauricio Avila



Ref. Certif. No.

US-45012-UL

Factory(ies):

XP POWER (VIETNAM) CO LTD
LOT D - 4Q - CN
My Phuoc 3 Industrial Park
Ben Cat District Binh Duong, Binh Duong,
Vietnam

XP POWER (KUNSHAN) LTD
230 BIN JIANG NAN RD
ZHANGPU TOWN KUNSHAN, Jiangsu, 215300
China

XP Power LLC
455 E. Trimble Road San Jose, CA 95131
United States

Additional Ratings:

HPT5K0TS400:
3-Phase (3W+PE), 50/60 Hz
Input 200-240V, 11A MAX/PHASE
Input 380-480V, 10A MAX/PHASE
Output:
0-400Vdc, 12.5A MAX
3000W MAX (with 200-240V input)
5000W MAX (with 380-480V input)

HPT5K0TS800:
3-Phase (3W+PE), 50/60 Hz
Input 200-240V, 11A MAX/PHASE
Input 380-480V, 10A MAX/PHASE
Output:
0-800Vdc, 6.25A MAX
3000W MAX (with 200-240V input)
5000W MAX (with 380-480V input)

Additionally evaluated to:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)



- ☒ UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- ☐ UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- ☐ UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- ☐ UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-03-26

Signature:

Mauricio Avila