



Ref. Certif. No.

**DK-174789-UL**

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME**

**CB TEST CERTIFICATE**

Product	Switching Power Supply
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory	No.88, Zong Lv Road, Zhonglou Economic Development Zone Changzhou, Jiangsu, 213100 China <input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Input: 100-240Vac, 50/60Hz, 2A, Output: See test report for detail
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	LBA100USx-yy <input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>
Additional information (if necessary may also be reported on page 2)	National Differences: EU Group Differences, CA, JP, CH, US <input checked="" type="checkbox"/> <a href="#">Additional Information on page 2</a>
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2023
As shown in the Test Report Ref. No. which forms part of this Certificate	2025112256251313-00 issued on 2025-12-09

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Denmark), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-12-22

Signature:   
Thomas Wilson



Ref. Certif. No.

**DK-174789-UL**

**Factory(ies):**

6th Floor, Building T4, Haigu Technology Building, Luoqu Community, Shiyan Street Baoan District Shenzhen, Gd, China

**Additional Model Detail(s):**

LBA100USx-yy, (x=05, 12, 15, 24, 36, 48, representative output voltage is 5V, 12V, 15V, 24V, 36V, 48V. "yy" represents a space or any numeric letter, omit the last "-" when yy is a space, representative commercial use.)

**Additionally evaluated to:**

EN IEC 62368-1:2024, EN IEC 62368-1:2024/A11:2024

**Additional information (if necessary)**



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see [www.ul.com/ncbnames](http://www.ul.com/ncbnames)

Date: 2025-12-22

Signature:

Thomas Wilson