



Ref. Certif. No.

DK-174792-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	SWITCHING POWER SUPPLY
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100 Irvine, CA 92602 United States
Name and address of the factory	No.88, Zong Lv Road, Zhonglou Economic Development Zone Changzhou, Jiangsu, 213100 China Additional Information on page 2
Note: When more than one factory, please report on page 2	
Ratings and principal characteristics	Input: 100-240V~, 2A, 50/60Hz Output: See test report for details.
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	LBA150PSx-yy Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	National Differences: EU Group Differences, AR, AU, CA, CN, JP, KR, NZ, SA, US Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2025120350575412-00 issued on 2025-12-09

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Denko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-12-20

Signature:


Thomas Wilson



Ref. Certif. No.

DK-174792-UL

Factory(ies):

6th Floor, Building T4, Haigu Technology Building, Luoazu Community, Shiyan Street Baoan District Shenzhen, Gd, China

Additional Model Detail(s):

LBA150PSx-yy, (x=05, 12, 15, 24, 27, 36, 48, representative output voltage is 5V, 12V, 15V, 24V, 27, 36V, 48V. "y" = Any letter or number or blank, represents commercial use, omit the final "-" when y is a blank.)

Additionally evaluated to:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-12-20

Signature:

Thomas Wilson