



Ref. Certif. No.

DK-174028-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	SWITCHING POWER SUPPLY
Name and address of the applicant	XP POWER L L C 340 Commerce, Suite 100, Irvine, CA, 92602 United States
Name and address of the manufacturer	XP POWER L L C 340 Commerce, Suite 100, Irvine, CA, 92602 United States
Name and address of the factory	No.88, Zong Lv Road, Zhonglou Economic Development Zone, Changzhou Jiangsu 213100, China
Note: When more than one factory, please report on page 2	<input checked="" type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	Input: LBA350PSXX-YYYYYYY: 100-240VAC, 4.5A, 50/60Hz LBA200PSXX-YYYYYYY: 100-240VAC, 3A, 50/60Hz Output: See test report for details
Trademark / Brand (if any)	
Customer's Testing Facility (CTF) Stage used	
Model / Type Ref.	LBA200PSXX-YYYYYYY, LBA350PSXX-YYYYYYY <input checked="" type="checkbox"/> Additional Information on page 2
Additional information (if necessary may also be reported on page 2)	National Differences: EU Group Differences, AR, AU, CA, CN, JP, KR, NZ, SA, US <input checked="" type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2018
As shown in the Test Report Ref. No. which forms part of this Certificate	2025111726111893-00 issued on 2025-11-25

This CB Test Certificate is issued by the National Certification Body



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-12-01

Signature:
Thomas Wilson



Ref. Certif. No.

DK-174028-UL

Factory(ies):

6th Floor, Building T4, Haigu Technology Building, LuoZu Community, Shiyan Street Baoan District, Shenzhen, Gd China

Additional Model Detail(s):

LBA200PSXX-YYYYYY, LBA350PSXX-YYYYYY, XX=12, 15, 24, 27, 36, 48, represents an output voltage of 12V, 15V, 24V, 27V, 36V, 48V.

YYYYYY = any alphanumeric character, a dash, any punctuation marks, or blank for marketing purposes

Additionally evaluated to:

EN IEC 62368-1:2020, EN IEC 62368-1:2020/A11:2020

Additional information (if necessary)



- UL Solutions (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL Solutions (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL Solutions (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL Solutions (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2025-12-01

Signature:

Thomas Wilson