

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST
CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME

SYSTEME CEI D'ACCEPTATION MUTUELLE DE
CERTIFICATS D'ESSAIS DES EQUIPEMENTS
ELECTRIQUES (IECEE) METHODE OC

CB TEST CERTIFICATE
CERTIFICAT D'ESSAI OC

Product
Produit

Switching Power Adapter

Name and address of the applicant
Nom et adresse du demandeur

XP Power
Horseshoe Park,
Pangbourne, Berkshire, RG8 7JW, United Kingdom

Name and address of the manufacturer
Nom et adresse du fabricant

XP Power
Horseshoe Park,
Pangbourne, Berkshire, RG8 7JW, United Kingdom

Name and address of the factory
Nom et adresse de l'usine

☒ Additional Information page 2

Note: When more than one factory, please report on page 2
Note: Lorsque il y plus d'une usine, veuillez utiliser la 2^{ème} page

Ratings and principal characteristics
Valeurs nominales et caractéristiques principales

AC 100-240V; 47-63Hz; 0.6-0.4A; Class II;
for output ratings refer to test report page 4

Trade mark (if any)
Marque de fabrique (si elle existe)

XP

Model/type Ref.
Ref. de type

PDM30USX-YY
(X = 05, 09, 12, 15, 18 or 24 for different output ratings;
YY = a-z, 0-9 or blank for different output ratings)

Additional information (if necessary may also be
reported on page 2)
Les Information complémentaire (si nécessaire,
peuvent être indiqués sur la 2^{ème} page)

Models differ in model name and output ratings; all models
have similar construction and differ slightly in transformer
sources and in secondary components.

A sample of the product was tested and found
to be in conformity with
Un échantillon de ce produit a été essayé et a été
considéré conforme à la

PUBLICATION **EDITION**
IEC 60601-1:1988+A1+A2
for national deviations see test report

As shown in the Test Report Ref. No. which forms part
of this Certificate
Comme indiqué dans le Rapport d'essais numéro de
référence qui constitue une partie de ce Certificat

11010814 001

This CB Test Certificate is issued by the National Certification Body
Ce Certificat d'essai OC est établi par l'Organisme National de Certification



TÜV Rheinland Group

TÜV Rheinland Product Safety GmbH
Am Grauen Stein · D-51105 Köln
Phone + 49 221 806-1400
Fax + 49 221 806-2095
Mail: cert-validity@de.tuv.com
Web: www.tuv.com



Date: 18.07.2007

Signature:

Dipl.-Ing. W. Hsu

1. No. 8-1, Fu Kung Rd.
Fu Hsing Park, Fu Hsing Hsiang
Chang Hua Hsien 506
Taiwan

2. Hsia-San-Chi Ind. Area, Bldg. 19
Dong-Cheng-Zhu-Shan Managing Area
523120 Dongguan, Kwangdong, China

Additional information (if necessary)
Information complémentaire (si nécessaire)

Date: 18.07.2007

Signature:

Dipl.-Ing. W. He



TEST REPORT	
IEC 601 -1	
Medical electrical equipment	
Part 1: General requirements for safety	
Report reference No.	11010814 001
Compiled by (+ signature).....	<i>Brian Huang</i>
Reviewed by (+ signature).....	<i>Angel Deltchev</i>
Approved by (+ signature).....	N/A
Date of issue.....	July 9 th , 2007
Testing laboratory	TÜV Rheinland Taiwan Ltd., Taichung Laboratory
Address.....	10F, No. 219, Min Chuan Rd. Taichung 403, Taiwan
Testing location.....	TÜV Rheinland Taiwan Ltd., Taichung Laboratory
Applicant	XP Power
Address.....	Horseshoe Park, Pangbourne, Berkshire RG8 7JW United Kingdom
Standard	IEC 60601-1: 1988 + A1:1991 + A2:1995 EN 60601-1 : 1990 + A1:1993 + A2:1995 +A13:1996
Test Report Form No.	I601-1_C/97-04
TRF Originator	Underwriters Laboratories Inc.
Master TRF	dated 97-04
Copyright blank test report.....	the bodies participating in the Committee of Certification Bodies (CCB). This report is based on a blank test report that was prepared by KEMA using information obtained from the TRF originator.
Test procedure.....	CB Scheme
Procedure deviation.....	N/A
Non-standard test method	N/A
Type of test object.....	Switching Power Adapter
Trademark	XP
Model/type reference	PDM30USX-YY (X= 05, 09, 12, 15, 18 or 24; YY= a-z, 0-9 or blank)
Manufacturer.....	Same as applicant
Address.....	Same as applicant
Rating.....	I/P: 100-240Vac, 47-63Hz, 0.6-0.4A O/P: See on page 4