

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**

CB TEST CERTIFICATE

Product

Open Frame Power Supply

Name and address of the applicant

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE, SUITE 100 TUSTIN, CA 92780 USA

Name and address of the factory

DI FENG GONG YE QU 2 HAO XIASHA LIUWU VLG SHIPAI
TOWN DONGGUAN GUANGDONG 523350
CHINA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

Input: 100-240Vac , 50-60Hz, 7-2.7A
Output: See test report for details.

Trademark / Brand (if any)



Type of Customer's Testing Facility (CTF) Stage used

Model / Type Ref.

UCH600PSxx
xx can be 12, 24, 36 or 48 for output voltage

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014/A11:2017; National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1:2014

As shown in the Test Report Ref. No. which forms part of this Certificate

PSE2019-0566 issued on 2019-12-02

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2019-12-12

Signature:

Jan-Erik Storgaard

For full legal entity names see www.ul.com/ncbnames