

The ITR03 series of single output unregulated converters are ideal for use in portable industrial and laboratory equipment.

Offering 3W in a small lightweight SIP4 package, the ITR03 provides a useful increase in power density over the similarly packaged 2W IL series and a cost saving over the semi-regulated IR series of more than 20% based on resales.



Features

- ▶ Unregulated single outputs from 5.0 to 15VDC
- ▶ $\pm 10\%$ input range
- ▶ SIP4 package
- ▶ 3kVDC functional isolation
- ▶ High efficiency up to 91%
- ▶ Complies with EN55032 class B
- ▶ -40°C to $+100^{\circ}\text{C}$ operating temperature
- ▶ Full power to $+85^{\circ}\text{C}$
- ▶ 3 year warranty

Applications



Dimensions

11.8 x 9.66 x 7.5mm (0.46" x 0.38" x 0.29")

Documentation

For further information click the link or scan the code

→ xppower.com



Models & ratings

Model number	Input voltage	Output voltage	Output current (full load)	Efficiency	Input current ⁽¹⁾		Maximum capacitive load ⁽²⁾
					No load	Full load	
ITR0305S05	4.5-5.5VDC	5.0VDC	600mA	83%	50mA	723mA	3300 μF
ITR0305S09		9.0VDC	333mA	87%	60mA	690mA	1200 μF
ITR0305S12		12.0VDC	250mA	88%	55mA	682mA	1000 μF
ITR0305S15		15.0VDC	200mA	88%	60mA	682mA	820 μF
ITR0312S05	10.8-13.2VDC	5.0VDC	600mA	85%	25mA	294mA	3300 μF
ITR0312S09		9.0VDC	333mA	89%	30mA	281mA	1200 μF
ITR0312S12		12.0VDC	250mA	90%	30mA	278mA	1000 μF
ITR0312S15		15.0VDC	200mA	91%	30mA	275mA	820 μF

Continued on page 2

Notes:

1. Input currents measured at nominal input voltage.
2. All specifications at $T_a = 25^{\circ}\text{C}$.

3. Standard tube quantity 40 pcs.

Models & ratings

Model number	Input voltage	Output voltage	Output current (full load)	Efficiency	Input current ⁽¹⁾		Maximum capacitive load ⁽²⁾
					No load	Full load	
ITR0324S05	4.5-5.5VDC	5.0VDC	600mA	83%	50mA	723mA	3300μF
ITR0324S09		9.0VDC	333mA	87%	60mA	690mA	1200μF
ITR0324S12		12.0VDC	250mA	88%	55mA	682mA	1000μF
ITR0324S15		15.0VDC	200mA	88%	60mA	682mA	820μF

Notes:

1. Input currents measured at nominal input voltage.
2. All specifications at Ta = 25°C.

3. Standard tube quantity 40 pcs.

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Input voltage range	4.5	5	4.5	VDC	ITR0305 series
	10.8	12	13.2		ITR0312 series
	21.6	24	26.4		ITR0324 series
Input filter	Integrated capacitor				
Input reflected ripple			20	mA pk-pk	Through 12μH inductor and 47μF capacitor
Input surge			7	VDC for 100ms	ITR0305 series
			15		ITR0312 series
			28		ITR0324 series

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Output voltage	5		15	VDC	See models and ratings table
Initial set accuracy			±3	%	See load regulation curves
Minimum load	10			%	Minimum load required for regulation
Line regulation			±1.2	%	Per 1% change in input voltage
Load regulation			±10	%	From 0 to 100% load
Transient response deviation			±5	% deviation	Recovery time 500μs, 25% load step change
Ripple & noise			100	mV pk-pk	Single output. 20MHz bandwidth. Measured using 0.1μF ceramic capacitor and 10μF electrolytic capacitor
Maximum capacitive load	See models and ratings table				
Temperature coefficient			0.02	%/°C	20MHz bandwidth, measured using 0.1μF ceramic capacitor

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Efficiency		88		%	See models and ratings table
Isolation: input to output	3000			VDC	Functional insulation. Working voltage 100Vrms
Switching frequency	40		70	kHz	
Isolation resistance	10 ⁹			Ω	Variable
Isolation capacitance			65	pF	
Power density			3.6 (59)	W/cm ³ (W/in ³)	MIL-HDBK-217F, +25°C GB
Mean time between failure	6.7			Mhrs	
Case material	Non conductive black plastic (UL94V-0 rated)				
Potting material	Silicon (UL94V-0 rated)				
Pin material	C5191R-H Solder-coated				
Solder process	JEDEC J-STD 020D.1. 260°C max. 1.5mm from case 10s max.				
Weight		2.2 (0.0048)		g (lb)	

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & conditions
Operating temperature	-40		+100	°C	See derating curve
Storage temperature	-55		+125	°C	
Case temperature			+115	°C	
Humidity			95	%RH	Non-condensing
Cooling	Natural convection				

Safety approvals

Safety agency	Standard	Notes & conditions
CE	Meets all applicable directives	
UKCA	Meets all applicable legislation	

Emissions - EMC


Phenomenon	Standard	Test level	Notes & conditions
Conducted	EN55032	Class B	External components required. See application notes.
Radiated	EN55032	Class B	

Immunity - EMC

Phenomenon	Standard	Test level	Criteria	Notes & conditions
ESD Immunity	EN61000-4-2	±8 kV	A	Air discharge
Radiated immunity	EN61000-4-3	10V/M	A	
EFT/Burst	EN61000-4-4	±2kV	A	External input capacitors required 100µF/250V
Surge	EN61000-4-5	±2kV	A	External input capacitors required 100µF/250V
Conducted immunity	EN61000-4-6	10 Vrms	A	
Magnetic fields	EN61000-4-8	100A/m	A	


Application notes

EMI filter




Model	C1	L
ITR0305	1206, 2.2µF, 50V	2.2µH
ITR0312	1206, 4.7µF, 50V	4.7µH
ITR0324	1206, 4.7µF, 50V	4.7µH

EFT/surge filter



Model	C2 & C3	D1
ITR0305	100µF, 250V	SMDJ8.0A
ITR0312	100µF, 250V	SMDJ16A
ITR0324	100µF, 250V	SMDJ30A


Derating curve




Application notes

Voltage regulation curves


ITR03xxS05




ITR03xxS09



ITR03xxS12




ITR03xxS15




Application notes

Efficiency curves


ITR0305xxx




ITR0312xxx



ITR0324xxx



Mechanical details



Notes:

- 1. All dimensions are in mm (inches)
- 2. Weight: 2.2 (0.0048) g (lb) approx.
- 3. Pin pitch tolerance: ± 0.35 (± 0.014)
- 4. Pin diameter: 0.5 ± 0.05 (0.02 ± 0.002)
- 5. Case tolerance: ± 0.5 (± 0.02)