



Ref. Certif. No.

DK-70356-UL

**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE)
CB SCHEME**

CB TEST CERTIFICATE

Product

Switching Power Supply

Name and address of the applicant

XP POWER LTD
401 COMMONWEALTH DR
HAW PAR TECHNOCENTRE
LOBBY B, SINGAPORE

Name and address of the manufacturer

XP POWER L L C
15641 RED HILL AVE
SUITE 100
TUSTIN CA 92780 USA

Name and address of the factory

Note: When more than one factory, please report on page 2

DONGGUAN DONGCHENG ZHUSHAN CINCON
ELECTRONICS FACTORY
1 JING XIANG RD DONGCHENG FOREIGN TRADE
INDUSTRIAL PARK ZHUSHAN DONGCHENG DISTRICT
DONGGUAN 523128 GUANGDONG
CHINA

[Additional Information on page 2](#)

Ratings and principal characteristics

See Page 2



Trademark (if any)

Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 1

Model / Type Ref.

VCE10USXX
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014.
National Differences specified in the CB Test Report.

[Additional Information on page 2](#)

A sample of the product was tested and found to be in conformity with

IEC 62368-1(ed.2)

As shown in the Test Report Ref. No. which forms part of this Certificate

E346017-A6005-CB-1 issued on 2018-01-30

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-01-31

Signature:

Jan-Erik Storgaard



Ref. Certif. No.

DK-70356-UL

Model Details:

VCE10USXX (where XX can be any number 03, 05, 09, 12, 15, 24, 48 designating the output voltage), may also be provided with suffix "-P" optionally for open frame type.

Factories:

CINCON ELECTRONICS CO LTD
8-1 FU KUNG RD FU HSING PARK FU HSING HSIANG CHANGHUA HSIEN 506
TAIWAN

Ratings:

Input Rated: 100-277 Vac, 0.3 A, 50/60 Hz

Output Rated:

- Model VCE10US03: Output Rated: 3.3 Vdc (2.95 - 3.65 Vdc), 2.40 A max., 8 W max.;
- Model VCE10US05: Output Rated: 5 Vdc (4.5 - 5.5 Vdc), 2 A max., 10W max.;
- Model VCE10US09: Output Rated: 9 Vdc (8.1 - 10 Vdc), 1.11 A max., 10W max.;
- Model VCE10US12: Output Rated: 12Vdc (10.1 - 13.5 Vdc), 0.83 A max., 10W max.;
- Model VCE10US15: Output Rated: 15Vdc (13.5 - 17 Vdc), 0.67 A max., 10W max.;
- Model VCE10US24: Output Rated: 24Vdc (21.1 - 26 Vdc), 0.42 A max., 10W max.;
- Model VCE10US48: Output Rated: 48Vdc (42.1 - 52 Vdc), 0.21 A max., 10W max.

Additional information (if necessary)



- UL (US), 333 Pflingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-01-31

Signature: 
Jan-Erik Storgaard