




Ref. Certif. No.

US-33043-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product	Switching Power Supply
Name and address of the applicant	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the manufacturer	XP POWER L L C 15641 RED HILL AVE, SUITE 100 TUSTIN CA 92780 UNITED STATES
Name and address of the factory <small>Note: When more than one factory, please report on page 2</small>	CHANNEL WELL TECHNOLOGY (GUANGZHOU) CO LTD BLDG B EASTERN HI-TECH INDUSTRIAL BASE ZENGJIANG STR, ZENGCHENG GUANGZHOU GUANGDONG 511300 CHINA <input type="checkbox"/> Additional Information on page 2
Ratings and principal characteristics	See Page 2
Trademark (if any)	
Type of Customer's Testing Facility (CTF) Stage used	CTF Stage 3
Model / Type Ref.	VFT80USXX Where XX is 05, 12, 15, 16, 18, 19, 20, 24, 30.
Additional information (if necessary may also be reported on page 2)	Additionally evaluated to EN 62368-1:2014 / A11:2017; National Differences specified in the CB Test Report. <input type="checkbox"/> Additional Information on page 2
A sample of the product was tested and found to be in conformity with	IEC 62368-1:2014
As shown in the Test Report Ref. No. which forms part of this Certificate	E317867-A6032-CB-1 issued on 2019-01-02

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

Date: 2019-01-08

Signature:

Jolanta M. Wroblewska

For full legal entity names see www.ul.com/ncbnames



Ref. Certif. No.

US-33043-UL

Ratings:

For Model VFT80US05

INPUT ~ 100-240 VAC; 1.7A; 50-60Hz

OUTPUT : 5V dc 12A 60W max

For Model VFT80US12

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 12V dc 6.66A 80W max

For Model VFT80US15

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 15V dc 5.33A 80W max

For Model VFT80US16

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 16V dc 5A 80W max

For Model VFT80US18

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 18V dc 4.44A 80W max

For Model VFT80US19

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 19V dc 4.21A 80W max

For Model VFT80US20

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 20V dc 4A 80W max

For Model VFT80US24

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 24V dc 3.33A 80W max

For Model VFT80US30

INPUT ~ 100-240 VAC; 2.0A; 50-60Hz

OUTPUT : 30V dc 2.66A 80W max

Additional information (if necessary)



UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN

UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2019-01-08

Signature:

Jolanta M. Wroblewska