



Ref. Certif. No.

US-31347-UL

IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT (IECEE) CB SCHEME

CB TEST CERTIFICATE

Product

Power supply for building-in, switch mode type

Name and address of the applicant

XP POWER L L C
SUITE 100
15641 RED HILL AVE
TUSTIN CA 92780 USA

Name and address of the manufacturer

XP POWER L L C
SUITE 100
15641 RED HILL AVE
TUSTIN CA 92780 USA

Name and address of the factory

XP POWER L L C
990 BENECIA AVE SUNNYVALE CA 94085
USA

Note: When more than one factory, please report on page 2

Additional Information on page 2

Ratings and principal characteristics

XTL30-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++:
180-264 Vac, (3W+PE), 50/60 Hz, 14A MAX Per Phase
(208Vac nominal, +/-10% Tolerance)
See Page 2

Trademark (if any)



Type of Customer's Testing Facility (CTF) Stage used

CTF Stage 3

Model / Type Ref.

XTL15-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++,
XTL30-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++
See Page 2

Additional information (if necessary may also be reported on page 2)

Additionally evaluated to EN 62368-1:2014;
National Differences specified in the CB Test Report.

Additional Information on page 2

A sample of the product was tested and found to be in conformity with

IEC 62368-1(ed.2)

As shown in the Test Report Ref. No. which forms part of this Certificate

E139109-D11-CB-2 issued on 2018-02-28

This CB Test Certificate is issued by the National Certification Body



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2018-03-01

Signature:

Jolanta M. Wroblewska



Ref. Certif. No.

US-31347-UL

Model Details:

XTL15-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++,
XTL30-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++
(Where M can be blank or a combination of a number 1, 2, 3, 4, or 5 or a letter A-Z; where P can be any number 0-9 or blank: where S can be any number 0-9 or blank: where + can be any number 0-9 or blank)

Factories:

XP POWER (KUNSHAN) LIMITED
230, BIN JIANG NAN ROAD, ZHANG PU TOWN KUNSHAN, JIANGSU 215300
CHINA

XP POWER (VIETNAM) CO LTD
LOT D - 4Q – CN MY PHUOC 3 INDUSTRIAL PARK BEN CAT DISTRICT BINH DUONG
VIET NAM

XP POWER PLC
HOESHOE PARK PANGBOURNE RG87 JW
UNITED KINGDOM

Ratings:

XTL30-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++:
180-264 Vac, (3W+PE), 50/60 Hz, 14A MAX Per Phase
(208Vac nominal, +/-10% Tolerance)

XTL15-MMMMMMMMMM-PPSS++/MMMMMMMMMM-PPSS++:
180-264 Vac, (3W+PE), 50/60 Hz, 7A MAX Per Phase
(208Vac nominal, +/-10% Tolerance)

Output rated: See model differences for details.

Additional information (if necessary)



- UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA
- UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK
- UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN
- UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/nbcnames

Date: 2018-03-01

Signature:

Jolanta M. Wroblewska