

75W Baseplate cooled

DC-DC converters 

The QSB75 series offers a compact 75W DC-DC converter solution in an industry standard ¼ brick package, with integral baseplate for conduction cooling. Available in two input ranges, covering 9V to 36VDC & 18V to 75VDC.

Standard features are: output voltage trim, remote sense, remote On/Off, a wide operating temperature range and includes protection for over current, over temperature and over voltage.

The QSB75 is highly suited to telecommunications, distributed power architectures, battery operated equipment, industrial electronics, mobile equipment and many other applications.



Features

- ▶ Regulated single outputs 3.3V to 24VDC
- ▶ 4:1 input ranges 9V to 36VDC & 18V to 75VDC
- ▶ Baseplate cooled ¼ brick package
- ▶ 1.5kVDC isolation
- ▶ Output trim $\pm 10\%$
- ▶ Remote sense
- ▶ Remote On/Off
- ▶ -40°C to $+100^{\circ}\text{C}$ operating temperature
- ▶ 3 year warranty

Applications



Dimensions

57.9 x 36.8 x 12.7mm (2.28" x 1.45" x 0.5")
¼ brick package

More resources

Click the link or scan the code

→ [xppower.com](https://www.xppower.com)



Models & ratings

| Model number ⁽³⁾ | Input voltage | Output voltage | Output current | Input current ⁽⁴⁾ | | Efficiency |
|-----------------------------|-----------------------------|----------------|----------------|------------------------------|-----------|------------|
| | | | | No load | Full load | |
| QSB7524S3V3 | 9-36VDC (24VDC nominal) | 3.3VDC | 12.00A | 50mA | 2.04A | 81.0% |
| QSB7524S05 | | 5.0VDC | 12.00A | 50mA | 2.98A | 84.0% |
| QSB7524S12 | | 12.0VDC | 6.25A | 50mA | 3.64A | 86.0% |
| QSB7524S15 | | 15.0VDC | 5.00A | 50mA | 3.64A | 86.0% |
| QSB7524S24 | | 24.0VDC | 3.12A | 50mA | 3.63A | 86.0% |
| QSB7548S3V3 | 18-75VDC (48VDC nominal) | 3.3VDC | 12.00A | 30mA | 1.10A | 82.0% |
| QSB7548S05 | | 5.0VDC | 12.00A | 30mA | 1.47A | 85.0% |
| QSB7548S12 | | 12.0VDC | 6.25A | 30mA | 1.82A | 86.0% |
| QSB7548S15 | | 15.0VDC | 5.00A | 30mA | 1.80A | 87.0% |
| QSB7548S24 | | 24.0VDC | 3.12A | 30mA | 1.80A | 87.0% |

Notes:

1. Ripple & noise is measured with a 10 μF tantalum capacitor and 1.0 μF ceramic capacitor across output.
2. Logic compatibility: Ref to -ve input. Module On = open circuit. Module Off = $<0.8\text{VDC}$.
3. Add suffix 'N' to the model number to receive the unit with negative logic Remote On/Off.
4. Input current specified at 24VDC for 9-36VDC and 48VDC for 18-75VDC models.

Input

| Characteristic | Minimum | Typical | Maximum | Units | Notes & conditions |
|----------------------------------|------------------------------|---------|---------|-------|--------------------|
| Input voltage range | 9 | | 36 | VDC | 24VDC |
| | 18 | | 75 | | 48VDC |
| Undervoltage lockout | | 8.8 | | VDC | On (24VDC) |
| | | 8.0 | | | Off (9-36VDC) |
| Input surge | | 50 | | VDC | 24VDC (for 100ms) |
| | | 100 | | | 48VDC (for 100ms) |
| Input current | See models and ratings table | | | | |
| Input reverse voltage protection | None | | | | |
| Input filter | Pi type | | | | |

Output

| Characteristic | Minimum | Typical | Maximum | Units | Notes & conditions |
|--------------------------|--|---------|---------|----------|---|
| Output voltage trim | | ±10 | | % | See application notes |
| Initial set accuracy | | | ±1.5 | % | |
| Line regulation | | | ±0.2 | % | Measured from high line to low line |
| Load regulation | | | ±0.2 | % | Measured from 0-100% load |
| Transient response | | | 5 | % | Maximum deviation, recovery to within 1% in 500µs, 25% step load change |
| Start up delay | | 100 | | ms | |
| Ripple and noise | | | 100 | mV pk-pk | 3.3 & 5VDC, 20MHz bandwidth |
| | | | 150 | | 12 & 15VDC, 20MHz bandwidth |
| | | | 280 | | 24VDC, 20MHz bandwidth |
| Overvoltage protection | 115 | | 140 | % | |
| Short circuit protection | Continuous | | | | |
| Thermal shutdown | | >100 | | °C | Baseplate temperature |
| | | <70 | | | Restart |
| Temperature coefficient | | ±0.03 | | %/°C | |
| Current Limit | 110 | | 140 | % | Of nominal output |
| Remote On/Off | See models and ratings notes | | | | |
| Remote Sense | Compensates up to 10% of Vout nominal, total of output trim and remote sense | | | | |

General

| Characteristic | Minimum | Typical | Maximum | Units | Notes & conditions |
|----------------------------|----------------------------|--------------|---------|--|-------------------------|
| Efficiency | See models & ratings table | | | | |
| Isolation: input to output | 1500 | | | VDC | |
| Isolation: input to case | 1500 | | | VDC | |
| Isolation: output to case | 1500 | | | VDC | |
| Isolation resistance | 10 ⁷ | | | Ω | |
| Isolation capacitance | | 100 | | pF | |
| Switching frequency | | 300 | | kHz | |
| Power density | | 115.3 (45.4) | | W/cm ³ (W/in ³) | |
| Mean time between failure | | 730 | | khrs | MIL-HDBK-217F, +25°C GB |

Environmental

| Characteristic | Minimum | Typical | Maximum | Units | Notes & conditions |
|----------------------|------------------|---------|---------|-------|--------------------|
| Operating base plate | -40 | | +100 | °C | See derating curve |
| Storage temperature | -55 | | +105 | °C | |
| Operating humidity | | | 90 | %RH | Non-condensing |
| Cooling | Baseplate cooled | | | | |

EMC: emissions

| Phenomenon | Standard | Test level | Notes & conditions |
|------------|----------|------------|--------------------------|
| Conducted | EN55032 | A | With external components |
| Radiated | EN55032 | A | With external components |

EMC: Immunity

| Phenomenon | Standard | Test level | Criteria | Notes & conditions |
|--------------|-------------|------------|----------|--------------------|
| ESD immunity | EN61000-4-2 | 2 | B | |
| Radiated | EN61000-4-3 | 3V/m | A | |
| EFT/burst | EN61000-4-4 | Level 1 | A | |
| Surges | EN61000-4-5 | Level 1 | A | |
| Conducted | EN61000-4-6 | 3Vrms | A | |

Safety approvals

| Safety agency | Standard | Test level | Notes & conditions |
|---------------|----------------------------------|------------|--------------------|
| UL | UL60950-1 | | |
| EN | EN62368-1 | | |
| CE | Meets all applicable directives | | |
| UKCA | Meets all applicable legislation | | |

Application notes

Output Voltage Trim

Voltage trim up

Connect trim resistor R_{trim} between Trim pin and -Sense pin.

$$R_{trim\ up} = \left(\frac{R1 \left(V_r - V_f \left(\frac{R2}{R2 + R3} \right) \right)}{V_{des} - V_{nom}} \right) - \frac{R2 \times R3}{R2 + R3} \text{ (k}\Omega\text{)}$$

Voltage trim down


Connect trim resistor R_{trim} between Trim pin and +Sense pin

$$R_{trim\ down} = \frac{R1 \times (V_{des} - V_r)}{V_{nom} - V_{des}} - R2 \text{ (k}\Omega\text{)}$$

Where: R trim up/down is the external resistor in k Ω . V_{nom} is the nominal output voltage. V_{des} is the desired output voltage. $R1$, $R2$, $R3$ and V_r are internal to the unit and are defined in the table below.

| Output Voltage (V) | R1(k Ω) | R2 (k Ω) | R3 (k Ω) | Vr (V) | Vf (V) |
|--------------------|-----------------|------------------|------------------|--------|--------|
| 3.3VDC | 3.00 | 12.0 | 4.3 | 1.24 | 0.46 |
| 5.0VDC | 2.32 | 3.3 | 0.0 | 2.5 | 0.00 |
| 12.0VDC | 9.10 | 51.0 | 5.1 | 2.5 | 0.46 |
| 15.0VDC | 12.0 | 56.0 | 8.25 | 2.5 | 0.46 |
| 24.0VDC | 20.0 | 100.0 | 7.5 | 2.5 | 0.46 |


Derating curve



| Air Flow Rate | Typical Rca |
|---|-------------|
| Natural Convection 0.56m³/min (0.1m/s) | 10.1°C/W |
| 2.83m³/min (0.5m/s) | 8.0°C/W |
| 5.66m³/min (1.0m/s) | 5.4°C/W |
| 8.49m³/min (1.5m/s) | 4.4°C/W |
| 11.32m³/min (2.0m/s) | 3.4°C/W |

Rca = Thermal resistance from case to ambient

Mechanical details



| Pin connections | |
|-----------------|---------------|
| Pin | Function |
| 1 | +Vin |
| 2 | Remote On/Off |
| 3 | -Vin |
| 4 | -Vout |
| 5 | -Sense |
| 6 | Trim |
| 7 | +Sense |
| 8 | +Vout |

Notes:

- Dimensions are in mm (inches)
- Tolerances: x.xx (x.x) = ± 0.5 (± 0.02), x.xxx (x.xx) = ± 0.25 (± 0.01)

3. Weight: 66g (0.15lbs) approx