



Product Service

CERTIFICATE

No. B 057396 0755 Rev. 00

Holder of Certificate: **XP Power LLC.**
15641 Red Hill Avenue, Suite 100
Tustin CA 92780
USA

Certification Mark:




Product: **Medical power supplies
(AC ADAPTER)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the testing and certification regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 081-210750-000

Valid until: 2026-05-06

Date, 2021-11-22


(Watson Yang)



CERTIFICATE

No. B 057396 0755 Rev. 00

Model(s): **AQM300PSxxyyyyyyyy**
 ('xx' can be 12, 15, 19, 24 or 48 to denote different output voltage, 'y' can be -, 0 to 9, a to z, A to Z or blank to denote market purpose)

Brand Name: **XP Power**



Parameters:

Rated input voltage:	100-240 Vac
Rated input current:	3.5-1.5 A
Rated frequency:	50-60 Hz
Rated outputs of models:	See below
Protection class:	I
Max. ambient temperature:	40 °C
Degree of protection against ingress of liquids:	IPX0

Tested according to: EN 60601-1:2006/A1:2013








CERTIFICATE

No. B 057396 0755 Rev. 00

License Conditions:

1. The product provides Means of Patient Protection (MOPP).
2. The equipment is evaluated for operating in altitude up to 3,000 m.
3. The product does not have direct connection to the patient.
4. Compliance with the requirements of IEC/EN 60601-1-2 (EMC) shall be evaluated at the end system.
5. Risk Management was included in this investigation
6. The following clauses were not part of the manufacturers order and therefore excluded from this testing:
 - 11.7: Biocompatibility of ME EQUIPMENT and ME SYSTEMS
 - 12.2: USABILITY
 - 17: Electromagnetic compatibility of ME EQUIPMENT and ME SYSTEMS
8. Model differences:

Models	Output Rated
AQM300PS12yyyyyyyy	12.0V  24.0A, 288.0W
AQM300PS15yyyyyyyy	15.0V  20.0A, 300.0W
AQM300PS19yyyyyyyy	19.0V  15.79A, 300.01W
AQM300PS24yyyyyyyy	24.0V  12.5A, 300.0W
AQM300PS48yyyyyyyy	48.0V  6.25A, 300.0W