



Product Service

CERTIFICATE

No. B 065969 0315 Rev. 00

Holder of Certificate: **XP Power Limited**

19 Tai Seng Avenue
#07-01
Singapore 534054
SINGAPORE

Certification Mark:



Product:

**Switching power supply unit
(Switching Power Supply)**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 652101805402

Valid until: 2029-07-21

Date, 2024-07-22

(Rickyet Wang)

CERTIFICATE

No. B 065969 0315 Rev. 00

Model(s): DSR240PS24, DSR240PS24y,
DSR240PS24yy, DSR240PS24yyy,
DSR240PS24yyyy, DSR240PS48,
DSR240PS48y, DSR240PS48yy,
DSR240PS48yyy, DSR240PS48yyyy
(y= 0 to 8 or -, only for marketing purpose)

Brand Name: XP



Parameters:

Rated Input: 100-240VAC, 50/60Hz, 3A max.

Rated Output: See below table for details

Protection Class: I

Degree of Protection: IPX0

Remark:

- Built-in type equipment, suitable enclosure should be provided in end system.
- When installing the equipment, all requirements of the relevant standard must be fulfilled.

Model	Rated output voltage (VDC)	Rated output current (A)	Max. rated output Power (W)
DSR240PS24, DSR240PS24y, DSR240PS24yy, DSR240PS24yyy, DSR240PS24yyyy	24	10	240
DSR240PS48, DSR240PS48y, DSR240PS48yy, DSR240PS48yyy, DSR240PS48yyyy	48	5	240

Tested according to: EN IEC 62368-1:2020/A11:2020