



Product Service

# CERTIFICATE

No. B 057396 0383 Rev. 01

**Holder of Certificate:** **XP Power LLC.**  
15641 Red Hill Avenue, Suite 100  
Tustin CA 92780  
USA

**Certification Mark:**



**Product:** **Power supply**

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition the certification holder must not transfer the certificate to third parties. See also notes overleaf.

**Test report no.:** 095-72143850K-000

**Valid until:** 2024-04-22

**Date,** 2019-05-02

*William A. Wenthold*  
( William A. Wenthold )

ZERTIFIKAT • CERTIFICATE • 認證書 • CERTIFICADO • CERTIFICAT

A4 / 07.17



Product Service

# CERTIFICATE

No. B 057396 0383 Rev. 01

**Model(s):**

**FCM400PSxx**

(where xx can be number 12 to 48 to indicate the main output voltage, can be provided with additional suffix "SF" for single pole fusing and/or "S" for screw input terminal)

**Brand Name:**

**XP**



## Parameters:

Rated Input Voltage: 100-240 VAC

Rated Input Current: 5 A

Rated input frequency: 50/60 Hz

Protection Class: I at end use.

Temperature, Ambient: 50°C with 100% rated output power

70°C with 50% rated output power

Elevation for use: 0-3048m above sea level

## Approved models and output ratings:

Model Number	MAIN OUTPUT RATING			Standby Output Rating	
	Voltage (VDC )	Maximum Current (A)	Maximum Output Power (W)	Voltage (VDC )	Current (A)
FCM400PS12	12	33.3	400	5	0.5
FCM400PS15	15	26.6	400	5	0.5
FCM400PS24	24	16.6	400	5	0.5
FCM400PS28	28	14.2	400	5	0.5
FCM400PS36	36	11.1	400	5	0.5
FCM400PS48	48	8.3	400	5	0.5

## Conditions of Acceptability:

When installing the equipment, all requirements of the standards and the manufacturer's specifications must be met.

ZERTIFIKAT • CERTIFICATE • CERTIFICADO • CERTIFIKAT • 認證證書 • CERTIFICATE



Product Service

# CERTIFICATE

No. B 057396 0383 Rev. 01

The models require:

- A suitable electrical and fire enclosure must be provided in the end use equipment.
- The following output circuits are at ES1 energy levels: All
- The following output circuits are at PS3 energy levels: All
- Heatsinks are floating and considered live. They should not be accessible in the end-product.
- A suitable main disconnect device shall be provided at the end product.
- Proper bonding to the end-product main protective earthing terminal is required at end product, sufficient clearance and creepage distance shall be provided between the primary circuit and accessible metal parts.
- Ground bond test, touch current test and dielectric Strength test need to be considered at end use equipment.
- The power supplies may have a fuse in the neutral of the primary circuit. The need for a marking to warn a service person of the hazards associated with double pole/neutral fusing shall be considered in the end product.

**Tested according to:** EN 62368-1:2014/A11:2017

**Production Facility(ies):** 059061, 071712, 059319, 089850

TUV SÜD  
ZERTIFIKAT ◆ CERTIFICATE ◆ 認證證書 ◆ CERTIFICADO ◆ CERTIFICAT

A4 / 07.17

