



Product Service

CERTIFICATE

No. B 057396 0979 Rev. 00

Holder of Certificate: **XP Power LLC.**
340 Commerce, Suite 100
Irvine CA 92602
USA

Certification Mark:




Product: **Adaptors**
(Medical Power Supply)

The product was tested on a voluntary basis and complies with the essential requirements. The certification mark shown above can be affixed on the product. It is not permitted to alter the certification mark in any way. In addition, the certification holder must not transfer the certificate to third parties. This certificate is valid until the listed date, unless it is cancelled earlier. All applicable requirements of the Testing, Certification, Validation and Verification Regulations of TÜV SÜD Group have to be complied. For details see: www.tuvsud.com/ps-cert

Test report no.: 081-241002-000

Valid until: 2028-08-03

Date, 2024-10-15


(Watson Yang)

CERTIFICATE

No. B 057396 0979 Rev. 00

Model(s): **AQM450PSxxyyyyyyyy**
 (xx can be 12, 19, 24, 48 or 56 for output voltage;
 y can be 0 to 9, a to z, A to Z or blank to denote
 market purpose)

Brand Name: **XP Power**


Parameters:

Rated input voltage:	100-240 Vac
Rated input current:	5.3-2.2 A
Rated frequency:	50-60 Hz
Rated outputs:	See below
Protection class:	I
Max. ambient temperature:	40 °C
Degree of protection against ingress of liquids:	IPX0

License Conditions:

- The product provides Means of Patient Protection (MOPP).
- The product has specified to operate at altitude $\leq 5,000$ m
- The product does not have direct connection to the patient.
- Compliance with EMC requirements needs to be evaluated for the end use product.
- The following clauses were not part of the manufacturers order and therefore excluded from this testing:
 - 11.7: Biocompatibility of ME EQUIPMENT and ME SYSTEMS
 - 12.2: USABILITY
 - 17: Electromagnetic compatibility of ME EQUIPMENT and ME SYSTEMS
 - 4.2: risk Management process for me equipment or me systems
- Model Differences:

Models \ Part	Output Rated
AQM450PS12	12 V $\overline{---$, 33.34 A, 400.08 W
AQM450PS19	19 V $\overline{---$, 23.6 A, 448.4 W
AQM450PS24	24 V $\overline{---$, 18.75 A, 450.0 W
AQM450PS48	48 V $\overline{---$, 9.38 A, 450.24 W
AQM450PS56	56 V $\overline{---$, 8.05 A, 450.8 W

Tested according to: EN 60601-1:2006/A2:2021